



SPECIFICATION SHEET

17-SDG325



KUT GARD® SEAMLESS KNIT SPUN DYNEEMA® / NYLON / NUARAMID GLOVE – MEDIUM WEIGHT

- Seamless knit construction provides comfort without sacrificing dexterity
- Medium weight spun Dyneema®, nylon & nuaramid shell provides excellent dexterity, tactile sensitivity and cut resistance
- Excellent for use as a glove liner
- Cotton color binding denotes sizing
- Elastic closure sewn inside glove for safety and comfort
- Launderable for extended life and to reduce replacement costs
- Made from component materials that comply with Federal Regulations for food contact 21CFR, 170-199
- Dyneema® is a brand of polyethylene fibers that are 10 to 15 times stronger than steel, more durable than polyester and a strength that is 40% greater than aramid fiber

APPLICATIONS

- Food processing
- Can also be used as glove liners

CARE INSTRUCTIONS

Recommend washing gloves in slightly warm water not exceeding 104°F (40°C). A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Hang dry, tumble dry is not recommended.

TECHNICAL DATA

MATERIAL	Spun Dyneema® / Nylon / Nuaramid			
CONSTRUCTION	7 gauge			
COLOR	■ Gray			
CUFF STYLE	Continuous knit			
SIZES	S - XL			
PACKAGING	1 pair per bag, 12 pairs per dozen, 6 dozen per case			
CASE DIMENSIONS	20.0" x 13.0" x 16.0" / 50.8cm x 33cm x 40.6cm			
CASE WEIGHT	S	M	L	XL
	10.5 lbs 4.7 kg	10.8 lbs 4.9 kg	12 lbs 5.4 kg	12.3 lbs 5.6 kg
COO	USA			

CUT RESISTANCE PROPERTIES

- ASTM F2992-15 ANSI Cut Level A2 (Adopted by ANSI/ISEA 02/16)
- ASTM F1790-05 ANSI Cut Level 2

BARCODES

ITEM	BAG	DOZEN	CASE
■ 17-SDG325/S	---	01616314059437	02616314059436
■ 17-SDG325/M	---	01616314059147	02616314059146
■ 17-SDG325/L	---	01616314058362	02616314058361
■ 17-SDG325/XL	---	01616314059154	02616314059153



DIMENSIONS (in/cm)

	S	M	L	XL
A	8.5 / 21.6	10.0 / 25.4	10.25 / 26.0	10.5 / 26.7
B	4.0 / 10.2	4.5 / 11.4	4.5 / 11.4	4.5 / 11.4
H	□ White	■ Red	■ Yellow	■ Gray

