



SPECIFICATION SHEET

19-D313



3544

G-TEK® 3GX, 13 GAUGE DYNEEMA® DIAMOND BLENDED SHELL WITH LATEX COATED PALM

- Washable, resistant to chemicals, water and ultraviolet light.
- Seamless construction
- Latex "Crinkle" coating provides superior grip in wet/dry conditions and offers abrasion resistance
- Dyneema® Diamond blended shell is lightweight and provides excellent dexterity, tactile sensitivity and cut resistance
- Compliant with FDA Part 177 - Indirect food activities: Polymers. Subpart C - Substances for use only as components of articles intended for repeated use. Sec. 177.2600
- Cotton color binding denotes sizing

APPLICATIONS

- Electronics
- Glass cutting
- Sheet metal handling
- Parts assembly
- Sharp small parts handling
- Construction
- Other general duty applications

CARE INSTRUCTIONS

Recommend washing gloves in slightly warm water not exceeding 40°C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Tumble dry on low - maximum temperature 140°F (60°C)

TECHNICAL DATA

MATERIAL	Shell: Dyneema® Diamond / Coating: Latex			
COLOR	Shell: ☐ White / Coating: ☒ Blue			
CUFF STYLE	Continuous Knit			
SIZES	S - XL			
PACKAGING	12 pairs per dozen, 6 dozen per case			
CASE	11.8" x 12.6" x 14.2" / 30cm x 32cm x 36cm			
CASE WEIGHT	S	M	L	XL
	13.7 lbs 6.2 kg	15.4 lbs 7 kg	16.5 lbs 7.5 kg	17.9 lbs 8.1 kg
COO	China			

PERFORMANCE PROPERTIES

EN388: 3544 ASTM F2992-15 ANSI Cut Level A4 (Adopted by ANSI/ISEA 02/16)
ASTM F1790-05 ANSI Cut Level 4

ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5

BARCODES

ITEM	BAG	DOZEN	CASE
☐ 19-D313/S	616314167409	01616314167408	02616314167407
☐ 19-D313/M	616314167393	01616314167392	02616314167391
☐ 19-D313/L	616314167386	01616314167385	02616314167384
☐ 19-D313/XL	616314167416	01616314167415	02616314167414



DIMENSIONS (in/cm)

	S	M	L	XL
A	9.1 / 23	9.4 / 24	9.8 / 25	10.2 / 26
B	3.9 / 10	4.1 / 10.5	4.3 / 11	4.5 / 11.5
H	☒ Red	☒ Yellow	☒ Brown	☒ Black

