



SPECIFICATION SHEET

19-D315



3543

G-TEK® 3GX, 15 GAUGE DYNEEMA® DIAMOND BLENDED SHELL WITH LATEX COATED PALM

- Washable, resistant to chemicals, water and ultraviolet light.
- Seamless construction
- Latex "Crinkle" coating provides superior grip in wet/dry conditions and offers abrasion resistance
- Dyneema® Diamond blended shell is lightweight and provides excellent dexterity, tactile sensitivity and cut resistance
- Compliant with FDA Part 177 - Indirect food activities: Polymers. Subpart C - Substances for use only as components of articles intended for repeated use. Sec. 177.2600
- Cotton color binding denotes sizing

APPLICATIONS

- Electronics
- Glass cutting
- Sheet metal handling
- Parts assembly
- Sharp small parts handling
- Construction
- Other general duty applications

CARE INSTRUCTIONS

Recommend washing gloves in slightly warm water not exceeding 40°C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Tumble dry on low - maximum temperature 140°F (60°C)

TECHNICAL DATA

MATERIAL	Shell: Dyneema® Diamond / Coating: Latex			
COLOR	Shell: ☐ White / Coating: ☒ Blue			
CUFF STYLE	Continuous Knit			
SIZES	S - XL			
PACKAGING	12 pairs per dozen, 6 dozen per case			
CASE	11.8" x 12.6" x 14.2" / 30cm x 32cm x 36cm			
CASE WEIGHT	S	M	L	XL
	13.2 lbs 6 kg	13.9 lbs 6.3 kg	15.4 lbs 7 kg	16.8 lbs 7.6 kg
COO	China			

PERFORMANCE PROPERTIES

EN388: 3543	ASTM F2992-15 ANSI Cut Level A4 (Adopted by ANSI/ISEA 02/16) ASTM F1790-05 ANSI Cut Level 4					
ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5

BARCODES

ITEM	BAG	DOZEN	CASE
☐ 19-D315/S	616314167447	01616314167446	02616314167445
☐ 19-D315/M	616314167430	01616314167439	02616314167438
☐ 19-D315/L	616314167423	01616314167422	02616314167421
☐ 19-D315/XL	616314167454	01616314167453	02616314167452



DIMENSIONS (in/cm)

	S	M	L	XL
A	9.1 / 23	9.4 / 24	9.8 / 25	10.2 / 26
B	3.7 / 9.5	3.9 / 10	4.1 / 10.5	4.3 / 11
H	☒ Red	☒ Yellow	☒ Brown	☒ Black

