



SPECIFICATION SHEET

20-TG SERIES



2-PLY SPUN DYNEEMA® / NYLON BLEND SLEEVES

- Spun Dyneema® and Nylon blend
- Offers unparalleled comfort and coolness while providing cut and abrasion resistance
- Seamless construction for comfort, fit and dexterity
- Elastic ends for a snug fit and to eliminate debris from entering
- Gray color is great for hiding dirt
- Color coded hems for easy size identification
- Launderable for extended life and to reduce replacement costs
- Made from component materials which comply with Federal regulations for food contact 21CFR 170-199
- Non-slip cuff provides superior fit (20-TG18NS model only)

APPLICATIONS

- Food processing
- Electronics manufacturing
- Glass cutting
- Paper processing

CARE INSTRUCTIONS

Recommend washing sleeves in slightly warm water not exceeding 40C. A mild non-ionic detergent should be used. A 5 - 10 minute cycletime should be employed. Hang dry, tumble dry is not recommended.

CUT RESISTANT PROPERTIES

- ASTM F2992-15 ANSI Cut Level A2 (Adopted by ANSI/ISEA 02/16)
- ASTM F1790-05 ANSI Cut Level 2

TECHNICAL DATA

MATERIAL	2-Ply Spun Dyneema®			
CUFF STYLE	Knit Cuff			
COLOR	Gray			
SIZES	14", 16", 18", 21"			
PACKAGING	144 each per case			
CASE DIMENSIONS	20" x 13" x 16" / 50.8cm x 33.2cm x 40.6cm			
CASE WEIGHT (LBS / KG)	14"	16"	18"	21"
	7 / 3.2	7.5 / 3.4	8 / 3.6	10 / 4.5
COO	USA			

BARCODES

ITEM	EACH	DOZEN	CASE
20-TG14	----	01616314058959	02616314058958
20-TG16	----	01616314058966	02616314058965
20-TG18	----	01616314058973	02616314058972
20-TG20	----	01616314066053	02616314066052
20-TG18NS (non-slip cuff)	----	01616314118240	026163140118249



DIMENSIONS (in/cm)

	14"	16"	18"	21"
A	14 / 35.6	16 / 40.6	18 / 45.7	21 / 53.3
B	2.75 / 6.9	2.75 / 6.9	2.75 / 6.9	2.75 / 6.9

