



SPECIFICATION SHEET

22-600



KUT GARD® SEAMLESS KNIT POLYKOR™ BLENDED ANTIMICROBIAL GLOVE – HEAVY WEIGHT

- Seamless knit construction provides comfort, fit, and dexterity
- PolyKor™ engineered yarns offer exceptional cut and slash resistance
- Ambidextrous pattern permits glove to be worn on either hand, extending wear and reducing costs
- Special non-latex cuff dramatically reduces cuff blowout, even after multiple launderings in bleach
- Can be worn on its own or as a glove liner
- Good gripping properties
- Shrink resistant
- Made from component materials that comply with Federal Regulations for food contact 21 CFR, 170-199
- Antimicrobial gloves are non-toxic and non-corrosive and complies with FDA, EPA, NSF and USDA standards for food contact

APPLICATIONS

- Food service and processing
- Glass and metal handling

CARE INSTRUCTIONS

Machine wash in warm water with detergent. Rinse well and spin using low speed. Tumble dry on low to medium heat setting. Temperature settings not to exceed 149°F (65°C). Can be dry-cleaned.

TECHNICAL DATA

MATERIAL	PolyKor™ / Stainless Steel / Synthetic Fibers
CONSTRUCTION	7 gauge ambidextrous seamless knit
COLOR	□ White
CUFF STYLE	Knitted elasticized wrist
SIZES	XS - XL
PACKAGING	24 each per case
CASE DIMENSIONS	12.0" x 6.0" x 6.0" / 30.5cm x 15.3cm x 15.3cm
CASE WEIGHT	3.9 lbs / 1.8 kg
COO	USA

CUT RESISTANCE PROPERTIES

- ASTM F2992-15 ANSI Cut Level A9 (Adopted by ANSI/ISEA 02/16)
- ASTM F1790-05 ANSI Cut Level 5

BARCODES

ITEM	EACH	DOZEN	CASE
□ 22-600XS	616314017414	01616314017414	02616314017414
□ 22-600S	616314017421	01616314017421	02616314017421
□ 22-600M	616314017438	01616314017438	02616314017438
□ 22-600L	616314017445	01616314017445	02616314017445
□ 22-600XL	616314017452	01616314017452	02616314017452



DIMENSIONS (in/cm)

	XS	S	M	L	XL
A	8.5 / 21.6	9.0 / 22.9	10.0 / 25.4	10.5 / 26.7	11.0 / 27.9
B	3.75 / 9.5	4.0 / 10.2	4.5 / 11.4	4.5 / 11.4	4.75 / 12.1
H	■ Black	■ Yellow	■ Blue	□ White	■ Green

