



# SPECIFICATION SHEET

## 22-650



### KUT GARD® SEAMLESS KNIT POLYKOR™ BLENDED GLOVE – HEAVY WEIGHT

- Seamless knit construction provides comfort, fit, and dexterity
- PolyKor™ engineered yarns offer exceptional cut and slash resistance
- Ambidextrous pattern permits glove to be worn on either hand, extending wear and reducing costs
- Special non-latex cuff dramatically reduces cuff blowout, even after multiple launderings in bleach
- Can be worn on its own or as a glove liner
- Good gripping properties
- Shrink resistant
- Made from component materials that comply with Federal Regulations for food contact 21 CFR, 170-199

### APPLICATIONS

- Food service and processing
- Glass and metal handling

### CARE INSTRUCTIONS

Machine wash in warm water with detergent. Rinse well and spin using low speed. Tumble dry on low to medium heat setting. Temperature settings not to exceed 149°F (65°C). Can be dry-cleaned.

### TECHNICAL DATA

MATERIAL	PolyKor™ Engineered Yarn / Stainless Steel / Synthetic Fibers
CONSTRUCTION	7 gauge ambidextrous seamless knit
COLOR	■ Blue
CUFF STYLE	Knitted elasticized wrist
SIZES	XS - XL
PACKAGING	24 each per case
CASE DIMENSIONS	12.0" x 6.0" x 6.0" / 30.5cm x 15.3cm x 15.3cm
CASE WEIGHT	3.0 lbs / 1.4 kg
COO	USA



### DIMENSIONS (in/cm)


	XS	S	M	L	XL
<b>A</b>	8.5 / 21.6	9.0 / 22.9	10.0 / 25.4	10.5 / 26.7	11.0 / 27.9
<b>B</b>	3.75 / 9.5	4.0 / 10.2	4.5 / 11.4	4.5 / 11.4	4.75 / 12.1
<b>H</b>	■ Black	■ Yellow	■ Blue	□ White	■ Green

### CUT RESISTANCE PROPERTIES

- ASTM F2992-15 ANSI Cut Level A7 (Adopted by ANSI/ISEA 02/16)
- ASTM F1790-05 ANSI Cut Level 5

### BARCODES

ITEM	EACH	DOZEN	CASE
■ 22-650XS	616314017469	01616314017469	02616314017469
■ 22-650S	616314017476	01616314017476	02616314017476
■ 22-650M	616314017483	01616314017483	02616314017483
■ 22-650L	616314017490	01616314017490	02616314017490
■ 22-650XL	616314017407	01616314017407	02616314017407



**PROTECTIVE INDUSTRIAL PRODUCTS, INC. | BRINGING THE BEST OF THE WORLD TO YOU®**

AMERICAS: (800) 262-5755 • (518) 861-0133 | EUROPE: +34-96182-41-48 | AMEA: (ASIA, MIDDLE EAST, AFRICA) 852-2475-9228 | [www.pipglobal.com](http://www.pipglobal.com)

This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED.