



# SPECIFICATION SHEET

## 22-750G



### KUT GARD® SEAMLESS KNIT DYNEEMA® BLENDED ANTIMICROBIAL GLOVE – LIGHT WEIGHT

- Seamless knit construction provides comfort, fit, and dexterity
- Dyneema® blend enhances the gloves performance without sacrificing flexibility or dexterity and ensures maximum protection
- Ambidextrous pattern permits glove to be worn on either hand, extending wear and reducing costs
- Special non-latex cuff dramatically reduces cuff blowout, even after multiple launderings in bleach
- Can be worn on its own or as a glove liner
- Good gripping properties
- Shrink resistant
- Made from component materials that comply with Federal Regulations for food contact 21 CFR, 170-199
- Antimicrobial gloves are non-toxic and non-corrosive and complies with FDA, EPA, NSF and USDA standards for food contact

### APPLICATIONS

- Food service and processing
- Glass and metal handling

### CARE INSTRUCTIONS

Machine wash in warm water with detergent. Rinse well and spin using low speed. Tumble dry on low to medium heat setting. Temperature settings not to exceed 149°F (65°C). Can be dry-cleaned.

### TECHNICAL DATA

MATERIAL	Dyneema® / Stainless Steel / Synthetic Fibers
CONSTRUCTION	13 gauge ambidextrous seamless knit
COLOR	■ Gray
CUFF STYLE	Knitted elasticized wrist
SIZES	XS - XL
PACKAGING	24 each per case
CASE DIMENSIONS	12.0" x 6.0" x 6.0" / 30.5cm x 15.3cm x 15.3cm
CASE WEIGHT	2.3 lbs / 1.0 kg
COO	USA

### CUT RESISTANCE PROPERTIES

- ASTM F2992-15 ANSI Cut Level A5 (Adopted by ANSI/ISEA 02/16)
- ASTM F1790-05 ANSI Cut Level 4

### BARCODES

ITEM	EACH	DOZEN	CASE
■ 22-750GXS	616314037351	01616314037351	02616314037351
■ 22-750GS	616314037375	01616314037337	02616314037337
■ 22-750GM	616314037368	01616314037320	02616314037320
■ 22-750GL	616314033919	01616314037313	02616314037313
■ 22-750GXL	616314037382	01616314037344	02616314037344



### DIMENSIONS (in/cm)

	XS	S	M	L	XL
<b>A</b>	7.5 / 19.1	8.5 / 21.6	24.1 / 9.5	10.5 / 26.7	11.5 / 29.2
<b>B</b>	3.5 / 8.9	3.75 / 9.5	4.0 / 10.2	4.25 / 10.8	4.25 / 10.8
<b>H</b>	■ Black	■ Yellow	■ Blue	□ White	■ Green

