

RIMLESS

 MEETS ANSI
Z87.1+

DESCRIPTION

Reader offered in increments of +0.25 diopters...matching the exact reading power of your personal glasses.

- Magnification reader glasses are for the worker who needs to see up close
- The 28 mm wide reading magnifier provides the worker with enough lens area to view his work throughout the day
- Due to its lightweight, rimless design and thin, rubberized temples, the Z12R is one of the best fitting readers on the market today
- Gray rubber co-molded temples provide a secure fit
- Molded nose bridge design to fit the vast majority of users
- 9.25 Base curve lens



Polycarbonate lenses block 99.99% of the sun's ultraviolet rays. This ultraviolet protection has already been incorporated within the lens material when the lenses are being produced.

TECHNICAL DATA

LENS	
TYPE	One Piece
MATERIAL	Polycarbonate 99.99% UVA and UVB light absorption
THICKNESS	2.0 mm
BASE CURVE	9.25
FRAME	
DESIGN	Rimless
MATERIAL	Polycarbonate
SAFETY STANDARDS	
ANSI Z87.1+	Yes
CAN/CSA Z94.3	No
PACKAGING	
PACKAGING	12 pair per inner box, 144 pair per case
CASE SIZE	cm: 64 x 29.5 x 32.5 in: 25.2 x 11.6 x 12.8
CASE WEIGHT	7 kg / 15.4 lbs
SINGLE PAIR WEIGHT	33 g / 1.2 oz
COUNTRY OF ORIGIN	Taiwan

TREATED FRONT AND BACK WITH A CLEAR, SCRATCH-RESISTANT COATING FOR A MUCH HARDER SURFACE.

ITEM NUMBERS & BARCODES

ITEM #	DIOPTER	FRAME COLOR	LENS COLOR & COATING	UPC BARCODES		
				EACH	BOX	CASE
250-27-0010	+1.00	Clear/Gray	Clear, Anti-Scratch	616314062445	01616314062444	02616314062443
250-27-0012	+1.25	Clear/Gray	Clear, Anti-Scratch	616314062452	01616314062451	02616314062450
250-27-0015	+1.50	Clear/Gray	Clear, Anti-Scratch	616314045111	01616314045110	02616314045110
250-27-0017	+1.75	Clear/Gray	Clear, Anti-Scratch	616314062469	01616314062468	02616314062467
250-27-0020	+2.00	Clear/Gray	Clear, Anti-Scratch	616314045127	01616314045127	02616314045127
250-27-0022	+2.25	Clear/Gray	Clear, Anti-Scratch	616314062476	01616314062475	02616314062474
250-27-0025	+2.50	Clear/Gray	Clear, Anti-Scratch	616314045134	01616314045134	02616314045134
250-27-0027	+2.75	Clear/Gray	Clear, Anti-Scratch	616314062483	01616314062482	02616314062481
250-27-0030	+3.00	Clear/Gray	Clear, Anti-Scratch	616314045141	01616314045141	02616314045141
250-27-0115	+1.50	Gray	Gray, Anti-Scratch	616314045158	01616314045158	02616314045158
250-27-0120	+2.00	Gray	Gray, Anti-Scratch	616314045165	01616314045165	02616314045165
250-27-0125	+2.50	Gray	Gray, Anti-Scratch	616314045172	01616314045172	02616314045172
250-27-0130	+3.00	Gray	Gray, Anti-Scratch	616314045189	01616314045189	02616314045189

PROTECTIVE INDUSTRIAL PRODUCTS, INC.

800-262-5755 // 518-861-0144 fax // sales@pipusa.com // www.pipusa.com



This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED.