

SEMI-RIMLESS

MEETS ANSI
Z87.1+



DESCRIPTION

Unique styling that will command your attention with fit, comfort and a variety of technical lens treatments

- Lightweight, semi-rimless design offers extensive eye coverage and all day comfort
- Bayonet style temples with non-slip rubber pads provide a secure fit
- Adjustable rubber nose pads offer a custom fit
- Anti-Fog lens coating as standard (except on clear AR & polarized lenses)
- Also meets CSA Z94.3 requirements for Canada
- 9.5 Base curve lens



Polycarbonate lenses block 99.99% of the sun's ultraviolet rays. This ultraviolet protection has already been incorporated within the lens material when the lenses are being produced.

TECHNICAL DATA

LENS	
TYPE	Dual
MATERIAL	Polycarbonate 99.99% UVA and UVB light absorption
THICKNESS	2.2 mm
BASE CURVE	9.5
FRAME	
DESIGN	Semi-Rimless
MATERIAL	Polycarbonate/EVA
SAFETY STANDARDS	
ANSI Z87.1	Yes
CAN/CSA Z94.3	Yes
PACKAGING	
PACKAGING	12 pair per inner display box; 144 pair per case
CASE SIZE	cm: 59.3 x 36 x 40.5 in: 23.3 x 14.2 x 15.9
CASE WEIGHT	7.2 kg / 15.8 lbs
SINGLE PAIR WEIGHT	28 gr / 0.99 oz
COUNTRY OF ORIGIN	Taiwan
HARMONIZATION CODE	9004.90.0000
POLARIZED EYEWEAR	
PACKAGING	6 pair per inner display box; 72 pair per case
CASE SIZE	cm: 41 x 38 x 31.5 in: 16.2 x 15 x 12.4
CASE WEIGHT	3.8 kg / 8.4 lbs

IDEAL FOR INDUSTRIAL WORKERS, WAREHOUSE WORKERS & FORK LIFT DRIVERS

ITEM NUMBERS & BARCODES

			UPC BARCODES		
ITEM #	FRAME COLOR	LENS COLOR & COATING	EACH	BOX	CASE
250-33-0020	Gloss Black	Clear, Anti-Scratch/Anti-Fog	616314130328	01616314130327	02616314130326
250-33-0021	Gloss Black	Gray, Anti-Scratch/Anti-Fog	616314130335	01616314130334	02616314130333
250-33-0010	Gloss Black	Clear, Anti-Reflective/Anti-Scratch	616314130342	01616314130341	02616314130340
250-33-0226	Gloss Black	Indoor/Outdoor Blue, Anti-Scratch/Anti-Fog	616314130359	01616314130358	02616314130357
250-33-0041	Gloss Black	Polarized Gray, Anti-Scratch	616314130366	01616314130365	02616314130364
250-33-1020	Gloss Bronze	Clear, Anti-Scratch/Anti-Fog	616314130373	01616314130372	02616314130371
250-33-1024	Gloss Bronze	Brown, Anti-Scratch/Anti-Fog	616314130380	01616314130389	02616314130388
250-33-1010	Gloss Bronze	Clear, Anti-Reflective/Anti-Scratch	616314130397	01616314130396	02616314130395
250-33-1226	Gloss Bronze	Indoor/Outdoor Blue, Anti-Scratch/Anti-Fog	616314130403	01616314130402	02616314130401
250-33-1042	Gloss Bronze	Polarized Brown, Anti-Scratch	616314130410	01616314130419	02616314130418

PROTECTIVE INDUSTRIAL PRODUCTS, INC.

800-262-5755 // 518-861-0144 fax // sales@pipusa.com // www.pipusa.com



This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED.