

FULL FRAME

MEETS ANSI
Z87.1+



DESCRIPTION

This “sun” collection offers polarized and mirror plus lenses featuring an AR treatment to eliminate reflection

- Lightweight, full frame design offers all day comfort
- Bayonet temples are rubber co-molded for a secure fit
- Non-slip rubber nose pads provide a comfortable fit
- 8 Base curve lens



Polycarbonate lenses block 99.99% of the sun's ultraviolet rays. This ultraviolet protection has already been incorporated within the lens material when the lenses are being produced.

TECHNICAL DATA

LENS	
TYPE	Dual
MATERIAL	Polycarbonate 99.99% UVA and UVB light absorption
THICKNESS	2.2 mm
BASE CURVE	8
FRAME	
DESIGN	Full Frame
MATERIAL	Polycarbonate/TPR
SAFETY STANDARDS	
ANSI Z87.1	Yes
CAN/CSA Z94.3	No
PACKAGING	
PACKAGING	6 pair per inner display box; 72 pair per case
CASE SIZE	cm: 41 x 38 x 31.5 in: 16.2 x 15 x 12.4
CASE WEIGHT	4.0 kg / 8.8 lbs
SINGLE PAIR WEIGHT	31 gr / 1.1 oz
COUNTRY OF ORIGIN	Taiwan

IDEAL FOR WORKING UNDER THE HOT SUN FOR LONG PERIODS, ROOFING, OIL RIGS & FISHING BOATS

ITEM NUMBERS & BARCODES

ITEM #	FRAME COLOR	LENS COLOR & COATING	UPC BARCODES		
			EACH	BOX	CASE
250-47-0041	Black	Polarized Gray, Anti-Scratch/Anti-Fog	616314129193	01616314129192	02616314129191
250-47-0004	Black	Red Mirror Plus, Anti-Scratch/Anti-Reflective	616314129209	01616314129208	02616314129207
250-47-0005	Black	Silver Mirror Plus, Anti-Scratch/Anti-Reflective	616314129216	01616314129215	02616314129214
250-47-0006	Black	Blue Mirror Plus, Anti-Scratch/Anti-Reflective	616314129223	01616314129222	02616314129221
250-47-0007	Black	Gold Mirror Plus, Anti-Scratch/Anti-Reflective	616314129230	01616314129239	02616314129238
250-47-0020	Black	Clear, Anti-Scratch/Anti-Fog	616314157974	01616314157973	02616314157972
250-47-0021	Black	Gray, Anti-Scratch/Anti-Fog	616314157547	01616314157546	02616314157545
250-47-1008	Brown	Green Mirror Plus, Anti-Scratch/Anti-Reflective	616314129247	01616314129246	02616314129245
250-47-1042	Brown	Polarized Brown, Anti-Scratch/Anti-Fog	616314129254	01616314129253	02616314129252

PROTECTIVE INDUSTRIAL PRODUCTS, INC.

800-262-5755 // 518-861-0144 fax // sales@pipusa.com // www.pipusa.com



This document and the information contained herein is the property of Protective Industrial Products, Inc. (PIP) and may not be used or reproduced without permission. Product users should conduct all appropriate testing or other evaluations to determine the suitability of PIP products for a particular purpose or use within a particular environment. PIP DISCLAIMS ALL WARRANTIES OTHER THAN AS EXPRESSLY PROVIDED.