

RIMLESS


 MEETS ANSI
Z87.1+

DESCRIPTION

Our most popular visitor's glasses feature a large frame that can be used alone, or as an Over-The-Glass (OTG) style to fit all personal eyewear

- Polycarbonate unilens
- Large over-the-glass design fits over most prescription eyewear
- Can also be worn by itself as a safety glass
- Molded nose bridge design to fit the vast majority of users
- Indirect vent temples to reduce fogging
- Also meets CSA Z94.3 requirements for the items noted in the table below
- 4 Base curve lens




Polycarbonate lenses block 99.99% of the sun's ultraviolet rays. This ultraviolet protection has already been incorporated within the lens material when the lenses are being produced.

TECHNICAL DATA

LENS	
TYPE	One Piece
MATERIAL	Polycarbonate 99.99% UVA and UVB light absorption
THICKNESS	2.0 mm
BASE CURVE	4
FRAME	
DESIGN	Rimless
MATERIAL	Polycarbonate
SAFETY STANDARDS	
ANSI Z87.1+	Yes
CAN/CSA Z94.3	Yes
PACKAGING	
PACKAGING	12 pair per inner box, 144 pair per case
CASE SIZE	cm: 70 x 39.5 x 32.5 in: 27.6 x 15.6 x 12.8
CASE WEIGHT	8.4 kg / 18.6 lbs
DISPENSER BOX SIZE (12pk)	cm: 38.1 x 17.1 x 10.2 in: 15 x 6.75 x 4
SINGLE PAIR WEIGHT	1.3 oz / 38 g
COUNTRY OF ORIGIN	China or Malaysia

HELPS PROVIDE PROTECTION FROM PROJECTILES AND IMPACT IN GENERAL USE APPLICATIONS.

ITEM NUMBERS & BARCODES

ITEM #	FRAME COLOR	LENS COLOR & COATING	UPC BARCODES		
			EACH	BOX	CASE
 250-99-0900	Clear	Clear, Anti-Scratch	616314024771	01616314024771	02616314024771
250-99-0901	Gray	Gray, Anti-Scratch	616314025136	01616314025136	02616314025136
250-99-0980	Clear	Clear, Uncoated	616314025143	01616314025143	02616314025143
DISPENSER BOX	12 PACK				
250-99-0980DP	Clear	Clear, Anti-Scratch	616314027598	01616314027598	02616314027598