



SPECIFICATION SHEET

25-6 SERIES



KUT GARD® SINGLE-PLY POLYKOR™ BLENDED ANTIMICROBIAL SLEEVE WITH HOOK & LOOP TOP & CLIP

- The proprietary PolyKor™ blend provides exceptional cut resistance and overall performance
- Seamless knit construction provides comfort, fit and dexterity
- Special non-latex cuff dramatically reduces cuff blow-out, even after multiple launderings in bleach
- Meets FDA & USDA food handling requirements
- Features a Patented NSF/ANSI Standard 51 Conformant approved antimicrobial fiber that is FDA & EPA approved for food contact
- Antimicrobial fiber has been shown to inhibit the growth of microorganisms such as bacteria and mold that come in contact with the fiber up to 99.9%
- Antimicrobial properties will not wash out of the fiber and will last the life of the sleeve
- Antimicrobial sleeves are non-toxic and non-corrosive and complies with FDA, EPA, NSF and USDA standards for food contact

APPLICATIONS

- Food service and processing
- Pulp and paper processing
- Plastic molding
- Glass and metal handling

CARE INSTRUCTIONS

Can be washed in caustic detergents and bleach.

TECHNICAL DATA

| | |
|-----------------|---|
| MATERIAL | PolyKor™ / Stainless Steel / Synthetic Fibers |
| CONSTRUCTION | Seamless knit |
| CUFF STYLE | Hoop & loop closure with clip attachment |
| COLORS | <input type="checkbox"/> White |
| SIZES | 12", 18", 21" (custom lengths available) |
| PACKAGING | 1 per bag, 12 per dozen, 24 each per case |
| CASE DIMENSIONS | 12" x 6" x 6" / 30.5cm x 15.3cm x 15.3cm |
| CASE WEIGHT | 73 lbs / 3.3 kg |
| COO | USA |

CUT RESISTANCE PROPERTIES

- ASTM F2992-15 ANSI Cut Level A9 (Adopted by ANSI/ISEA 02/16)
- ASTM F1790-05 ANSI Cut Level 5

BARCODES

| ITEM | EACH | DOZEN | CASE |
|---------------------------------|--------------|----------------|----------------|
| <input type="checkbox"/> 25-612 | 616314017766 | 01616314017766 | 02616314017766 |
| <input type="checkbox"/> 25-618 | 616314017773 | 01616314017773 | 02616314017773 |
| <input type="checkbox"/> 25-621 | 616314017780 | 01616314017780 | 02616314017780 |



DIMENSIONS (in/cm)

| | 12" | 18" | 21" |
|---|------------|------------|------------|
| A | 12 / 30.5 | 18 / 45.7 | 21 / 53.3 |
| B | 5.3 / 13.5 | 5.3 / 13.5 | 5.3 / 13.5 |

