



SPECIFICATION SHEET

263-42003

SECURE™ 3 PASSIVE EAR MUFFS - CAP MOUNTED

- Fits most cap-style hard hats on the market with universal slots
- Ear cups can be placed in three positions... usage, stand-by to allow hearing, and storage up and away when not needed
- Slim profile design increases stability and reduces risk of snagging in confined spaces
- Smooth telescopic single-point size adjustment increases comfort, stability and wear time
- Soft and wide ear cushions feature snap-in system for easy replacement
- Dielectric, non-conductive

APPLICATIONS

- Low frequency noise
- Airport ground crew
- Motor racing
- Drill hammering

TECHNICAL DATA

MATERIAL	Ear Cups and Spacer: ABS thermoplastic Cushion: Polyether & PVC-foil Foam liner: Polyether Buckle and Arm: POM thermoplastic Spring Housing: POM thermoplastic 10% gf Screw for housing: Stainless steel Slot adaptor: PA 66 thermoplastic 10% gf Steel spring: Stainless spring steel
COLOR	Orange / Black
ATTENUATION	NRR: 27 dB / SNR: 31 dB
STYLE	Cap Mounted
SIZE	Adjustable
WEIGHT	10.6 oz / 300 g
PACKAGING	20 per case
CASE	22" x 13" x 11" / 56cm x 33cm x 28cm
CASE WEIGHT	17.6 lbs / 8 kg
COO	Sweden

BARCODES

ITEM	EACH	DOZEN	CASE
263-42003	7391441000333	---	7391441000333



ATTENUATION DATA

FREQUENCY HZ	125	250	500	1000	2000	3150	4000	6300	8000	NRR
Mean Attenuation dB	19.4	23.6	33.5	37.9	36.5	35.0	39.4	39.2	39.6	27
Standard Deviation dB	2.9	2.1	1.9	4.3	2.1	3.3	2.8	2.6	2.4	

Tested in accordance with ANSI standard S3.19-1974

Canada Class A (L)

FREQUENCY HZ	63	125	250	500	1000	2000	4000	8000	H	M	L	SNR
Mean Attenuation dB	16,4	17,7	23,5	31,8	41,6	36,4	34,2	35,2				31
Standard Deviation dB	4,3	3,3	4,2	3,5	3,4	3,8	3,9	5,7	32	29	21	
APV dB	12,1	14,4	19,3	28,3	38,2	32,6	30,3	29,5				