



# SPECIFICATION SHEET

## 270-2050

### N95 CONE RESPIRATOR WITH VALVE

- Exhalation valve for easier breathing, especially in hot and humid working conditions
- "N95" masks provide 95% filtration efficiency against airborne particles
- Not resistant to oil
- Low breathing resistance and a soft inner lining ensure all-day comfort
- Adjustable outside nosepiece (with inside foam padding) provides a proper fit
- Flanged mask edge for a comfortable fit, better face seal, less inward leakage and better fit testing results
- Latex-free braided head straps
- Ultrasonic welding of straps on wings (no staples)
- Easy to wear with clear and simple fitting instructions
- NIOSH approved

### APPLICATIONS

- Sanding
- Grinding
- Cleaning

### TECHNICAL DATA

MATERIAL	Polyester / Polypropylene
COLOR	<input type="checkbox"/> White
SIZES	One size with adjustable nose piece
PACKAGING	10 masks per box, 120 masks per case
CASE DIMENSIONS	21" x 17" x 7.5" / 53.3cm x 43.2cm x 19cm
CASE WEIGHT	0.6 lbs / 0.3 kg
COO	China

### BARCODES

ITEM	BAG	BOX	CASE
<input type="checkbox"/> 270-2050	---	01616314052308	02616314052307

