



SPECIFICATION SHEET

300-1000

NON-ANSI SURVEYOR'S STYLE SAFETY VEST WITH PRISMATIC TAPE

- Durable polyester solid front and breathable mesh fabric back
- Zipper closure
- Split trim 1" prismatic tape
- 2 upper external pockets with 1 left chest pen pocket
- 2 lower external flap pockets

APPLICATIONS

- Road construction
- Riggers
- Warehouses

CARE INSTRUCTIONS

Recommend washing in tempered water not exceeding 104°F or 40°C. Wash in a 5-10 minute cycle time or hand wash. Rinse in cold water. Tumble dry at temperature not exceeding 104°F or 40°C, do not wring. Do not wash in biological powder, wash as synthetics. Maximum of 10 wash cycles.

TECHNICAL DATA

MATERIAL	100% Polyester
CONSTRUCTION	Front: 120g/m ² 100% polyester tricoe fabric Back: 120g/m ² 100% polyester mesh fabric
COLOR	Red or Blue
SIZES	S-5X
PACKAGING	1 per polybag; 50 per case
CASE DIMENSIONS	18.9" x 11.8" x 19.3" / 48cm x 30cm x 49cm
CASE WEIGHT	34.2 lbs / 15.5 kg
COO	China

BARCODES

ITEM	BAG	BOX	CASE
300-1000-RD/S	616314205019	---	2616314205017
300-1000-RD/M	616314183812	---	2616314183810
300-1000-RD/L	616314183829	---	2616314183827
300-1000-RD/XL	616314183836	---	2616314183834
300-1000-RD/2X	616314183843	---	2616314183841
300-1000-RD/3X	616314183850	---	2616314183858
300-1000-RD/4X	616314183867	---	2616314183865
300-1000-RD/5X	616314183874	---	2616314183872
300-1000-BL/S	616314205002	---	2616314205000
300-1000-BL/M	616314183881	---	2616314183889
300-1000-BL/L	616314183898	---	2616314183896
300-1000-BL/XL	616314183904	---	2616314183902
300-1000-BL/2X	616314183911	---	2616314183919
300-1000-BL/3X	616314183928	---	2616314183926
300-1000-BL/4X	616314183935	---	2616314183933
300-1000-BL/5X	616314183942	---	2616314183940



DIMENSIONS (in/cm)

	S	M	L	XL	2X	3X	4X	5X
A	44.9 / 114	47.2 / 120	49.6 / 126	52 / 132	54.3 / 138	56.7 / 144	59 / 150	61.4 / 156
B	27 / 69	28 / 71	28 / 71	28 / 71	29 / 73.5	29 / 73.5	30 / 76	30 / 76

