



SPECIFICATION SHEET

302-0212



ANSI TYPE R CLASS 2 BREAKAWAY VEST

- 5 point breakaway
- Breathable polyester mesh
- 2" two-tone reflective tape for optimum visibility
- Hook and loop closure
- 2 external lower flap pockets
- 1 upper chest/radio pocket and 2 mic tabs

APPLICATIONS

- Construction
- Municipalities
- Railyards & Shipyards
- Anywhere hi-visibility apparel is necessary

CARE INSTRUCTIONS

Recommend washing in tempered water not exceeding 104°F or 40°C. Wash in a 5-10 minute cycle time or hand wash. Rinse in cold water. Tumble dry at temperature not exceeding 104°F or 40°C, do not wring. Do not wash in biological powder, wash as synthetics. Maximum of 25 wash cycles.

TECHNICAL DATA

MATERIAL	100% Polyester
CONSTRUCTION	Main: 120g/m ² polyester mesh Acc: 2-inch silver contrast reflective tape
COLOR	■ Hi-Vis Lime Yellow or ■ Hi-Vis Orange
SIZES	S - 5X
PACKAGING	1/Polybag, 50/Case
CASE	19" x 18" x 10" / 48.3cm x 45.7cm x 25.4cm
CASE WEIGHT	32.0 lbs / 14.5 kg
COO	China

BARCODES

ITEM	BAG	DOZEN	CASE
■ 302-0212-LY/S	616314204784	01616314204783	02616314204782
■ 302-0212-LY/M	616314170874	01616314170873	02616314170872
■ 3302-0212-LY/L	616314170881	01616314170880	02616314170889
■ 302-0212-LY/XL	616314170898	01616314170897	02616314170896
■ 302-0212-LY/2X	616314170904	01616314170903	02616314170902
■ 302-0212-LY/3X	616314170911	01616314170910	02616314170919
■ 302-0212-LY/4X	616314170928	01616314170927	02616314170926
■ 302-0212-LY/5X	616314170935	01616314170934	02616314170933
■ 302-0212-OR/S	616314204791	01616314204790	02616314204799
■ 302-0212-OR/M	616314169076	01616314169075	02616314169074
■ 302-0212-OR/L	616314169083	01616314169082	02616314169081
■ 302-0212-OR/XL	616314169090	01616314169099	02616314169098
■ 302-0212-OR/2X	616314169106	01616314169105	02616314169104
■ 302-0212-OR/3X	616314169113	01616314169112	02616314169111
■ 302-0212-OR/4X	616314169120	01616314169129	02616314169128
■ 302-0212-OR/5X	616314169137	01616314169136	02616314169135



DIMENSIONS (in/cm)

	S	M	L	XL	2X	3X	4X	5X
A	45/114	47/120	49.5/126	52/132	54.5/138	56.5/144	59/150	61.5/156
B	27/69	28/71	28/71	28/71	29/73.5	29/73.5	30/76	30/76
C	11.5/29	11.8/30	12/30.5	12.2/31	12.4/31.5	12.6/32	12.8/32.5	13/33

