



SPECIFICATION SHEET

302-MVGZ4P



ANSI TYPE R CLASS 2 FOUR POCKET VALUE MESH VEST

- Breathable polyester mesh
- Zipper closure
- 2" silver reflective tape
- 2 lower internal pockets
- 2 external chest pockets, 1 including 4 pen pockets

APPLICATIONS

- Construction
- Survey crews
- Utility workers
- Railway and metro workers
- Shipyards

CARE INSTRUCTIONS

Recommend washing in tempered water not exceeding 104°F or 40°C. Wash in a 5-10 minute cycle time or hand wash. Rinse in cold water. Tumble dry at temperature not exceeding 104°F or 40°C, do not wring. Do not wash in biological powder, wash as synthetics. Maximum of 30 wash cycles.

TECHNICAL DATA

MATERIAL	100% Polyester mesh
CONSTRUCTION	120g/m2 100% polyester 5*1 mesh fabric; silver reflective tape; #5 resin zipper
COLOR	■ Hi-Vis Lime Yellow ■ Hi-Vis Orange
SIZES	S - 5X
PACKAGING	1/Polybag, 50/Case
CASE	19.7" x 11" x 15" / 50cm x 28cm x 38cm
CASE WEIGHT	27 lbs / 12.2 kg
COO	China



DIMENSIONS (in/cm)

	S	M	L	XL	2X	3X	4X	5X
A	45/114	47.2/120	49.6/126	52/132	54.3/138	56.7/144	59/150	61.4/156
B	24/69	28/71.1	28/71.1	28/71.1	28/71.1	28/71.1	28/71.1	28/71.1

BARCODES

ITEM	BAG	DOZEN	CASE
■ 302-MVGZ4P-LY/S	01616314204547	---	02616314204546
■ 302-MVGZ4P-LY/M	01616314072429	---	02616314072428
■ 302-MVGZ4P-LY/L	01616314072412	---	02616314072411
■ 302-MVGZ4P-LY/XL	01616314072436	---	02616314072435
■ 302-MVGZ4P-LY/2X	01616314072375	---	02616314072374
■ 302-MVGZ4P-LY/3X	01616314072382	---	02616314072381
■ 302-MVGZ4P-LY/4X	01616314072399	---	02616314072398
■ 302-MVGZ4P-LY/5X	01616314072405	---	02616314072404
■ 302-MVGZ4P-OR/S	01616314204554	---	02616314204553
■ 302-MVGZ4P-OR/M	01616314072498	---	02616314072497
■ 302-MVGZ4P-OR/L	01616314072481	---	02616314072480
■ 302-MVGZ4P-OR/XL	01616314072504	---	02616314072503
■ 302-MVGZ4P-OR/2X	01616314072443	---	02616314072442
■ 302-MVGZ4P-OR/3X	01616314072450	---	02616314072459
■ 302-MVGZ4P-OR/4X	01616314072467	---	02616314072466
■ 302-MVGZ4P-OR/5X	01616314072474	---	02616314072473

