



SPECIFICATION SHEET

302-PSV-GRN



ANSI TYPE P CLASS 2 PUBLIC SAFETY VEST

- Breathable mesh top, durable solid bottom
- 5 point breakaway
- Off shoulder breakaway system for added comfort
- Adjustable hook & loop sides for universal fit
- 2 mic tabs with reinforced stitching
- Oversized lower internal pocket
- 1 external pen pocket on chest
- Breakaway zipper front closure

APPLICATIONS

- Safety personnel
- Security
- Law enforcement

CARE INSTRUCTIONS

Machine wash, 104°F max, 30 cycles. Always wear fastened.
The high visibility properties of this garment must be kept clean to be effective. If faded or permanently soiled it must be replaced with a new one.

TECHNICAL DATA

| | |
|-----------------|---|
| MATERIAL | 100% Polyester |
| CONSTRUCTION | Main: 110g/m2 100% polyester 5*1 mesh (FDY) fabric (green); 120g/m2 100% polyester tricot fabric (lime yellow) Acc: #5 resin zipper |
| COLOR | Hi-Vis Lime Yellow / Green |
| SIZES | M/5X, 2X/5X |
| PACKAGING | 1 per poly bag, 5 per inner pack, 50 per case |
| CASE DIMENSIONS | 18.9" x 11.8" x 13.8" / 48cm x 30cm x 35cm |
| CASE WEIGHT | 30 lbs / 13.6 kg |
| COO | China |

BARCODES

| ITEM | BAG | INNER PACK | CASE |
|-------------------|----------------|------------|----------------|
| 302-PSV-GRN/M-XL | 01616314073204 | --- | 02616314073203 |
| 302-PSV-GRN/2X-5X | 01616314073181 | --- | 02616314073180 |



DIMENSIONS (in/cm)

| | M/XL | 2X/5X |
|---|--------------------------|--------------------------|
| A | 44.1 / 112 | 49.2 / 125 |
| B | 24.4 / 62 | 24.4 / 62 |
| C | 4.5 x 3.5 / 11.43 x 8.89 | 4.5 x 3.5 / 11.43 x 8.89 |
| D | 9 x 4.5 / 22.86 x 11.43 | 9 x 4.5 / 22.86 x 11.43 |

