



SPECIFICATION SHEET

303-HSVE



ANSI TYPE R CLASS 3 VALUE 4 POCKET MESH VEST

- Breathable polyester mesh
- 2" silver reflective tape
- Hook and loop closure
- 2 external upper chest pockets
- 2 internal lower pockets

APPLICATIONS

- Construction
- Municipalities
- Shipyards
- Anywhere hi-visibility apparel is necessary

CARE INSTRUCTIONS

Recommend washing in tempered water not exceeding 104° F or 40° C. Wash in a 5-10 minute cycle time or hand wash. Rinse in cold water. Tumble dry at temperature not exceeding 104° F or 40° C, do not wring. Do not wash in biological powder, wash as synthetics. Maximum of 30 wash cycles.

TECHNICAL DATA

MATERIAL	100% Polyester mesh
CONSTRUCTION	Main: 120g/m ² mesh fabric and 120g/m ² tricot polyester knit Acc: 2-inch silver contrast reflective tape
COLOR	■ Hi-Vis Lime Yellow or ■ Hi-Vis Orange
SIZES	S - 5X
PACKAGING	1/Polybag, 50/Case
CASE SIZE	19.7" x 11" x 24.8" / 50cm x 28cm x 63cm
CASE WEIGHT	28 lbs / 12.7 kg
COO	China

BARCODES

ITEM	BAG	DOZEN	CASE
■ 303-HSVE-LY/S	01616314204981	---	02616314204980
■ 303-HSVE-LY/M	01616314071309	---	02616314071308
■ 303-HSVE-LY/L	01616314071293	---	02616314071292
■ 303-HSVE-LY/XL	01616314071316	---	02616314071315
■ 303-HSVE-LY/2X	01616314071255	---	02616314071254
■ 303-HSVE-LY/3X	01616314071262	---	02616314071261
■ 303-HSVE-LY/4X	01616314071279	---	02616314071278
■ 303-HSVE-LY/5X	01616314071286	---	02616314071285
■ 303-HSVE-OR/S	01616314204998	---	02616314204997
■ 303-HSVE-OR/M	01616314071378	---	02616314071377
■ 303-HSVE-OR/L	01616314071361	---	02616314071360
■ 303-HSVE-OR/XL	01616314071385	---	02616314071384
■ 303-HSVE-OR/2X	01616314071323	---	02616314071322
■ 303-HSVE-OR/3X	01616314071330	---	02616314071339
■ 303-HSVE-OR/4X	01616314071347	---	02616314071346
■ 303-HSVE-OR/5X	01616314071354	---	02616314071353



DIMENSIONS (in/cm)

	S	M	L	XL	2X	3X	4X	5X
A	45 / 114	47.2 / 120	49.6 / 126	52 / 132	54.3 / 138	56.7 / 144	59 / 150	61.4 / 156
B	27 / 69	28 / 71.1	28 / 71.1	28 / 71.1	28 / 71.1	28 / 71.1	28 / 71.1	28 / 71.1

