



SPECIFICATION SHEET

303-HSVP



ANSI TYPE R CLASS 3 VALUE TWO TONE MESH VEST

- Breathable polyester mesh
- 2" two tone tape for optimum visibility
- Zipper closure
- 2 internal lower pockets

APPLICATIONS

- Construction
- Municipalities
- Shipyards
- Anywhere hi-visibility apparel is necessary

CARE INSTRUCTIONS

Recommend washing in tempered water not exceeding 104° F or 40° C. Wash in a 5-10 minute cycle time or hand wash. Rinse in cold water. Tumble dry at temperature not exceeding 104° F or 40° C, do not wring. Do not wash in biological powder, wash as synthetics. Maximum of 30 wash cycles.

TECHNICAL DATA

MATERIAL	100% Polyester mesh
CONSTRUCTION	Main: 120g/m ² mesh fabric and 120g/m ² tricot polyester knit Acc: 2-inch silver contrast reflective tape
COLOR	■ Hi-Vis Lime Yellow or ■ Hi-Vis Orange
SIZES	S - 5X
PACKAGING	1/Polybag, 50/Case
CASE SIZE	22.8" x 14.6" x 13.8" / 58cm x 37cm x 35cm
CASE WEIGHT	23 lbs / 10.4 kg
COO	China

BARCODES

ITEM	BAG	DOZEN	CASE
■ 303-HSVP-LY/S	01616314204929	---	02616314204928
■ 303-HSVP-LY/M	01616314071484	---	02616314071483
■ 303-HSVP-LY/L	01616314071477	---	02616314071476
■ 303-HSVP-LY/XL	01616314071491	---	02616314071490
■ 303-HSVP-LY/2X	01616314071439	---	02616314071438
■ 303-HSVP-LY/3X	01616314071446	---	02616314071445
■ 303-HSVP-LY/4X	01616314071453	---	02616314071452
■ 303-HSVP-LY/5X	01616314071460	---	02616314071469
■ 303-HSVP-OR/S	01616314204936	---	02616314204935
■ 303-HSVP-OR/M	01616314071552	---	02616314071551
■ 303-HSVP-OR/L	01616314071545	---	02616314071544
■ 303-HSVP-OR/XL	01616314071569	---	02616314071568
■ 303-HSVP-OR/2X	01616314071507	---	02616314071506
■ 303-HSVP-OR/3X	01616314071514	---	02616314071513
■ 303-HSVP-OR/4X	01616314071521	---	02616314071520
■ 303-HSVP-OR/5X	01616314071538	---	02616314071537



DIMENSIONS (in/cm)

	S	M	L	XL	2X	3X	4X	5X
A	45 / 114	47.2 / 120	49.6 / 126	52 / 132	54.3 / 138	56.7 / 144	59 / 150	61.4 / 156
B	27 / 69	28 / 71.1	28 / 71.1	28 / 71.1	28 / 71.1	28 / 71.1	28 / 71.1	28 / 71.1

