



# SPECIFICATION SHEET

## 305-5PVFR



### ANSI TYPE R CLASS 2 TREATED SOLID BREAKAWAY VEST

- Solid polyester treated material to prevent after-flame
- Treatment good for up to 25 washes
- 5-point breakaway provides additional safety around extreme traffic hazards, moving machinery or equipment
- FR 2" silver reflective tape
- 2 internal lower pockets
- 1 external chest pocket
- Hook and loop closure
- 2 internal lower pockets
- 1 upper left chest pocket
- Dual sizes: S/M, L/XL, 2X/3X, 4X/5X

### APPLICATIONS

- Road construction
- Survey crews
- Shipyards and railyards
- Anywhere high visibility and limited flammability is needed
- Not designed for use in an ARC flash or flash fire application

### CARE INSTRUCTIONS

Machine wash in cold water, tumble dry low or hand dry. Do not iron, do not dry clean. Do not use bleach or fabric softener. Do not wash in biological powder, wash as synthetics. A chemical treatment is used to impart limited flammability that allows material to become self-extinguishing. Washing and wearing will diminish these properties.

### TECHNICAL DATA

MATERIAL	100% Polyester
CONSTRUCTION	120gm/m <sup>2</sup> treated Polyester Tricot 2" FR reflective tape Hook and loop closure
COLOR	Yellow or Orange
SIZES	S/M - 4X/5X
PACKAGING	1 per polybag; 50 per case
CASE DIMENSIONS	18.9" x 14.2" x 16.1" / 48cm x 36cm x 41cm
CASE WEIGHT	41.9 lbs / 19 kg
COO	China

### BARCODES

ITEM	BAG	BOX	CASE
305-5PVFRLY/S-M	01616314069764	---	02616314069763
305-5PVFRLY/L-XL	01616314069757	---	02616314069756
305-5PVFRLY/2X-3X	01616314069733	---	02616314069732
305-5PVFRLY/4X-5X	01616314069740	---	02616314069749
305-5PVFROR/S-M	01616314096920	---	02616314096929
305-5PVFROR/L-XL	01616314096890	---	02616314096899
305-5PVFROR/2X-3X	01616314096906	---	02616314096905
305-5PVFROR/3X-4X	01616314096913	---	02616314096912



### DIMENSIONS (in/cm)

	S / M	L / XL	2X / 3X	4X / 5X
A	47.2 / 120	52 / 132	56.7 / 144	61.4 / 156
B	28 / 71.1	28 / 71.1	28.9 / 73.5	29.9 / 76

