



SPECIFICATION SHEET

305-HSSVFR



ANSI TYPE R CLASS 3 FR TREATED SOLID VEST

- Solid polyester treated material to prevent after-flame
- Treatment good for up to 25 washes
- FR 2" silver reflective tape
- Hook and loop closure
- Available in hi-vis lime yellow and hi-vis orange

APPLICATIONS

- Road construction
- Survey crews
- Municipalities
- Shipyards / Railyards
- Anywhere high visibility and limited flammability is needed
- Not designed for use in an ARC flash or flash fire application

CARE INSTRUCTIONS

Machine wash in cold water, tumble dry low or hand dry. Do not iron, do not dry clean. Do not use bleach or fabric softener. Do not wash in biological powder, wash as synthetics. A chemical treatment is used to impart limited flammability that allows material to become self-extinguishing. Washing and wearing will diminish these properties.

TECHNICAL DATA

MATERIAL	100% Polyester
CONSTRUCTION	120gm/m ² treated polyester Tricot, 2" FR reflective tape, Hook and loop closure
COLOR	Yellow or Orange
SIZES	S/M - 4X/5X
PACKAGING	1 per polybag; 50 per case
CASE DIMENSIONS	18.9" x 14.2" x 16.1" / 48cm x 36cm x 41cm
CASE WEIGHT	41.9 lbs / 19 kg
COO	China



DIMENSIONS (in/cm)

	S / M	L / XL	2X / 3X	4X / 5X
A	47.2 / 120	52 / 132	56.7 / 144	61.4 / 156
B	28 / 71.1	28 / 71.1	28.9 / 73.5	29.9 / 76

BARCODES

ITEM	BAG	BOX	CASE
305-HSSVFRLY/S-M	01616314071743	---	02616314071742
305-HSSVFRLY/L-XL	01616314071736	---	02616314071735
305-HSSVFRLY/2X-3X	01616314071712	---	02616314071711
305-HSSVFRLY/4X-5X	01616314071729	---	02616314071728
305-HSSVFROR/S-M	01616314088611	---	02616314088610
305-HSSVFROR/L-XL	01616314088581	---	02616314088580
305-HSSVFROR/2X-3X	01616314088598	---	02616314088597
305-HSSVFROR/3X-4X	01616314088604	---	02616314088603

