



SPECIFICATION SHEET

305-MVFR



ANSI TYPE R CLASS 2 FR TREATED TWO TONE MESH VEST

- Mesh polyester treated material to prevent after-flame
- Treatment good for up to 25 washes
- FR 2" two tone tape
- 2 internal lower pockets
- Hook and loop closure
- Available in hi-vis lime yellow and orange
- Dual sizes: S/M, L/XL, 2X/3X, 4X/5X

APPLICATIONS

- Road construction
- Survey crews
- Shipyards / railyards
- Anywhere high visibility and limited flammability is needed
- Not designed for use in an ARC flash or flash fire application

CARE INSTRUCTIONS

Machine wash in cold water, tumble dry low or hand dry. Do not iron, do not dry clean. Do not use bleach or fabric softener. Do not wash in biological powder, wash as synthetics. A chemical treatment is used to impart limited flammability that allows material to become self-extinguishing. Washing and wearing will diminish these properties.

TECHNICAL DATA

MATERIAL	100% Polyester
CONSTRUCTION	120gm/m ² treated polyester mesh 2" FR silver reflective tape Hook and loop closure
COLOR	Yellow or Orange
SIZES	S/M - 4X/5X
PACKAGING	1 per polybag; 50 per case
CASE DIMENSIONS	18.9" x 14.2" x 15" / 48cm x 36cm x 38cm
CASE WEIGHT	32 lbs / 14.5 kg
COO	China

BARCODES

ITEM	BAG	BOX	CASE
305-MVFR/LY-S-M	01616314076779	---	02616314076778
305-MVFR/LY-L-XL	01616314076762	---	02616314076761
305-MVFR/LY/2X-3X	01616314076748	---	02616314076747
305-MVFR/LY/4X-5X	01616314076755	---	02616314076754
305-MVFR/OR-S-M	01616314088512	---	02616314088511
305-MVFR/OR-L-XL	01616314088529	---	02616314088528
305-MVFR/OR/2X-3X	01616314088536	---	02616314088535
305-MVFR/OR/3X-4X	01616314088543	---	02616314088542



DIMENSIONS (in/cm)

	S / M	L / XL	2X / 3X	4X / 5X
A	21.5 / 54.6	25.5 / 64.8	29.5 / 74.9	33.5 / 85.1
B	28 / 71.1	28 / 71.1	28 / 71.1	28 / 71.1

