



# SPECIFICATION SHEET

## 305-USV5FR



### ANSI TYPE R CLASS 2 EXPANDABLE FR TREATED MESH VEST

- Mesh polyester treated material to prevent after-flame
- Treatment good for up to 25 washes
- Adjustable sides for universal fit
- FR 2" silver reflective tape
- 2 internal lower pockets
- Hook and loop closure
- Available in hi-vis lime yellow and hi-vis orange
- Available in one size only

### APPLICATIONS

- Road construction
- Survey crews
- Shipyards / railyards
- Anywhere high visibility and limited flammability is needed
- Not designed for use in an ARC flash or flash fire application

### CARE INSTRUCTIONS

Machine wash in cold water, tumble dry low or hand dry. Do not iron, do not dry clean. Do not use bleach or fabric softener. Do not wash in biological powder, wash as synthetics. A chemical treatment is used to impart limited flammability that allows material to become self-extinguishing. Washing and wearing will diminish these properties.

### TECHNICAL DATA

MATERIAL	100% Polyester
CONSTRUCTION	120gm/m <sup>2</sup> treated polyester mesh fabric 2" FR reflective tape Hook and loop closure
COLOR	Yellow or Orange
SIZES	One size fits most
PACKAGING	1 per polybag; 50 per case
CASE DIMENSIONS	18.9" x 14.2" x 15" / 48cm x 36cm x 38cm
CASE WEIGHT	39.7 lbs / 18 kg
COO	China

### BARCODES

ITEM	BAG	BOX	CASE
305-USV5FRLY	01616314073976	---	02616314073975
305-USV5FROR	01616314088666	---	02616314088665



### DIMENSIONS (in/cm)

	ONE SIZE			
A	49.6 / 126	---	---	---
B	24.8 / 63	---	---	---

