



SPECIFICATION SHEET

305-WCENGFR



ANSI TYPE R CLASS 2 FR TREATED SOLID VEST

- Solid polyester treated material to prevent after-flame
- Treatment good for up to 25 washes
- FR 2" two tone tape
- 2 internal lower pockets
- Hook and loop closure
- Available in hi-vis lime yellow and hi-vis orange
- Dual sizes: S/M, L/XL, 2X/3X, 4X/5X

APPLICATIONS

- Road construction
- Survey crews
- Shipyards / railyards
- Anywhere high visibility and limited flammability is needed
- Not designed for use in an ARC flash or flash fire application

CARE INSTRUCTIONS

Machine wash in cold water, tumble dry low or hand dry. Do not iron, do not dry clean. Do not use bleach or fabric softener. Do not wash in biological powder, wash as synthetics. A chemical treatment is used to impart limited flammability that allows material to become self-extinguishing. Washing and wearing will diminish these properties.

TECHNICAL DATA

MATERIAL	100% Polyester
CONSTRUCTION	120gm/m ² treated tricot 2" FR silver reflective tape Hook and loop closure
COLOR	Yellow or Orange
SIZES	S/M - 4X/5X
PACKAGING	1 per polybag; 50 per case
CASE DIMENSIONS	18.9" x 14.2" x 15" / 48cm x 36cm x 38cm
CASE WEIGHT	32 lbs / 14.5 kg
COO	China



DIMENSIONS (in/cm)

	S / M	L / XL	2X / 3X	4X / 5X
A	21.5 / 54.6	25.5 / 64.8	29.5 / 74.9	33.5 / 85.1
B	28 / 71.1	28 / 71.1	28 / 71.1	28 / 71.1

BARCODES

ITEM	BAG	BOX	CASE
305-WCENGFRLY/S-M	01616314074294	---	02616314074293
305-WCENGFRLY/L-XL	01616314074287	---	02616314074286
305-WCENGFRLY/2X-3X	01616314074263	---	02616314074262
305-WCENGFRLY/4X-5X	01616314074270	---	02616314074279
305-WCENGFROR/S-M	01616314088659	---	02616314088658
305-WCENGFROR/L-XL	01616314088628	---	02616314088627
305-WCENGFROR/2X-3X	01616314088635	---	02616314088634
305-WCENGFROR/3X-4X	01616314088642	---	02616314088641

