



SPECIFICATION SHEET

310-1100



NON-ANSI LONG SLEEVE T-SHIRT

- 5 oz. polyester birdseye mesh
- ANSI compliant fabric
- Durable lightweight performance wicking fabric
- 1 chest pocket

APPLICATIONS

- Construction
- Municipalities
- Shipyards
- Anywhere high visibility is needed

CARE INSTRUCTIONS

Recommend washing in tempered water not exceeding 104°F or 40°C. Wash in a 5-10 minute cycle time or hand wash. Rinse in cold water. Tumble dry at low temperature not exceeding 140°F or 40°C, do not wring. Do not wash in biological powder, wash as synthetics. Maximum of 30 wash cycles.

TECHNICAL DATA

MATERIAL	100% Polyester
CONSTRUCTION	Main fabric: 140g/m ² 100% polyester bird eyes fabric; Accessories: 200g/m ² 100% polyester rib fabric
COLOR	■ Hi-Vis Lime Yellow or ■ Hi-Vis Orange
SIZES	S - 5X
PACKAGING	1 per polybag, 50 per case
CASE DIMENSIONS	21.7" x 13.8" x 15.7" / 55cm x 35cm x 40cm
CASE WEIGHT	26.5 lbs / 12 kg
COO	China

BARCODES

ITEM	BAG	BOX	CASE
■ 310-1100LY/S	616314113505	---	02616314113503
■ 310-1100LY/M	616314083013	---	02616314083011
■ 310-1100LY/L	616314083020	---	02616314083028
■ 310-1100LY/XL	616314083037	---	02616314083035
■ 310-1100LY/2X	616314083044	---	02616314083042
■ 310-1100LY/3X	616314083051	---	02616314083059
■ 310-1100LY/4X	616314083068	---	02616314083066
■ 310-1100LY/5X	616314083075	---	02616314083073
■ 310-11000R/S	616314113512	---	02616314113510
■ 310-11000R/M	616314082948	---	02616314082946
■ 310-11000R/L	616314082955	---	02616314082953
■ 310-11000R/XL	616314082962	---	02616314082960
■ 310-11000R/2X	616314082979	---	02616314082977
■ 310-11000R/3X	616314082986	---	02616314082984
■ 310-11000R/4X	616314082993	---	02616314082991
■ 310-11000R/5X	616314083006	---	02616314083004



DIMENSIONS (in/cm)

	S	M	L	XL	2X	3X	4X	5X
A	44 / 111.8	51.2 / 130	53.1 / 135	55.1 / 140	57.1 / 145	59.1 / 150	61 / 155	63 / 160
B	27.5 / 70	28.3 / 72	29.1 / 74	29.9 / 76	30.7 / 78	31.5 / 80	32.3 / 82	33.1 / 84

