



SPECIFICATION SHEET

319-MTP



RIPSTOP REINFORCED OVERPANT

- High-visibility ANSI class E polyester mesh pants, yellow with contrast trim, 2 side access pockets, 2-inch 3M silver reflective tape
- 100% polyester mesh
- Elastic draw string waist
- 2 side access pockets
- Fully taped seams
- 2-inch 3M silver reflective tape

APPLICATIONS

- Construction
- Municipalities
- Shipyards
- Anywhere hi-visibility apparel is necessary

CARE INSTRUCTIONS

Recommend washing in tempered water not exceeding 104°F or 40°C. Washing in a 5-10 minute cycle time or hand wash. Rinse in cold water. Tumble dry at temperature not exceeding 104°F or 40°C, do not wring. Do not wash in biological powder, wash as synthetics. Maximum of 10 wash cycles.

TECHNICAL DATA

MATERIAL	100% Polyester
CONSTRUCTION	Main: 110g/m ² 100% Polyester mesh Acc: 2" 3M silver tape, 120g/m ² 100% polyester mesh warning tape
COLOR	■ Hi-Vis Lime Yellow
SIZES	S/M, L/XL, 2X/3X, 4X/5X
PACKAGING	1/Polybag, 50/Case
CASE	26.8" x 13.4" x 5.9" / 68cm x 34cm x 15cm
CASE WEIGHT	33 lbs / 15 kg
COO	China
HARM CODE	6117.90.9070

BARCODES

ITEM	BAG	DOZEN	CASE
■ 319-MTP-LY - S/M	01616314071989	---	02616314071988
■ 319-MTP-LY - L/XL	01616314071972	---	02616314071971
■ 319-MTP-LY - 2X/3X	01616314071958	---	02616314071957
■ 319-MTP-LY - 4X/5X	01616314071965	---	02616314071964



DIMENSIONS (in/cm)

	S/M	L/XL	2X/3X	4X/5X
A	47.0 / 119.4	53.5 / 135.9	60.0 / 152.4	66.0 / 167.6
B	29.0 / 73.7	32.0 / 81.3	32.5 / 82.6	34.0 / 86.4
C	21.0 / 53.3	24.5 / 62.2	26.0 / 66.0	27.5 / 69.8

