



SPECIFICATION SHEET

33-115



SEAMLESS KNIT POLYESTER GLOVE WITH POLYURETHANE COATED SMOOTH GRIP ON PALM & FINGERS

- Seamless knit nylon shell offers increased comfort, finger dexterity and breathability
- Polyurethane (PU) coatings offer great puncture and abrasion resistance while offering excellent tactile sensitivity
- Knit Wrist helps prevent dirt and debris from entering the glove
- Breathable back for comfort
- Pair packed for ease of distribution

APPLICATIONS

- Electronic and computer assembly
- Quality control
- Inspection
- General assembly
- Touch screen devices

CARE INSTRUCTIONS

Recommend washing gloves in tempered water not exceeding 104° F or 40°C. A mild non-ionic laundry soap or detergent should be used. Wash in a 5-10 minute cycle time. Rinse in cold water. Tumble dry at temperature not exceeding 140° F or 60° C.

TECHNICAL DATA

MATERIAL	Polyester with polyurethane coating on palm and fingers					
COLOR	☐ White					
CUFF STYLE	Continuous Knit					
SIZES	XS - XXL					
PACKAGING	1 pair per bag, 12 pairs per dozen, 25 dozen per case					
CASE	24.8" x 11.0" x 18.1" / 63cm x 28cm x 46cm					
CASE WEIGHT	XS	S	M	L	XL	XXL
	14.2 lbs 6.4 kg	15.6 lbs 7.1 kg	16 lbs 7.3 kg	17 lbs 7.7 kg	18 lbs 8.2 kg	19.1 lbs 8.7 kg
COO	China					

PERFORMANCE PROPERTIES

EN388: 3121						
ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5

BARCODES

ITEM	PAIR	DOZEN	CASE
☐ 33-115/XS	616314164972	01616314164971	02616314164970
☐ 33-115/S	616314164958	01616314164957	02616314164956
☐ 33-115/M	616314164941	01616314164940	02616314164949
☐ 33-115/L	616314164934	01616314164933	02616314164932
☐ 33-115/XL	616314164965	01616314164964	02616314164963
☐ 33-115/XXL	616314164989	01616314164988	02616314164987



DIMENSIONS (in/cm)

	XS	S	M	L	XL	XXL
A	8.46 / 21.5	9 / 23	9.4 / 24	9.8 / 25	10.2 / 26	10.6 / 27
B	3.5 / 9	3.6 / 9.2	3.7 / 9.5	3.8 / 9.8	4 / 10.2	4.3 / 11
H	☐ Purple	☐ Red	☐ Yellow	☐ Brown	☐ Black	☐ Blue

