



SPECIFICATION SHEET

33-125



G-TEK® SEAMLESS KNIT NYLON GLOVE WITH POLYURETHANE COATED SMOOTH GRIP

- 13 gauge, seamless knit nylon shell offers increased comfort, finger dexterity and breathability
- Polyurethane (PU) coatings offer great puncture and abrasion resistance while offering excellent tactile sensitivity
- Knit wrist helps prevent dirt and debris from entering the glove
- Breathable back for comfort
- This style is also available tri-folded and shrink-wrapped for carefree dispensing through vending machines (33-125V)

APPLICATIONS

- Electronic and computer assembly
- Quality control
- Inspection
- General assembly

CARE INSTRUCTIONS

Recommend washing gloves in tempered water not exceeding 104° F or 40°C. A mild non-ionic laundry soap or detergent should be used. Wash in a 5-10 minute cycle time. Rinse in cold water. Tumble dry at temperature not exceeding 104° F or 60° C.

TECHNICAL DATA

MATERIAL	Nylon with polyurethane coating on palm and fingers					
COLOR	☐ White					
CUFF STYLE	Continuous Knit					
SIZES	XS - XXL					
PACKAGING	1 pair per bag, 12 pairs per dozen, 25 dozen per case					
CASE	24.4" x 11.1" x 18.1" / 62cm x 28cm x 46cm					
CASE WEIGHT	XS	S	M	L	XL	XXL
	18.7 lbs 8.5 kg	19.8 lbs 9.0 kg	20.9 lbs 9.5 kg	22.0 lbs 10.0 kg	23.1 lbs 10.5 kg	24.3 lbs 11.0 kg
COO	China					



DIMENSIONS (in/cm)

	XS	S	M	L	XL	XXL
A	7.5 / 19.0	8.5 / 21.5	8.9 / 22.5	9.3 / 23.5	9.6 / 24.5	10.0 / 25.5
B	3.2 / 8.2	3.3 / 8.4	3.4 / 8.7	3.7 / 9.5	3.9 / 9.9	4.1 / 10.3
H	■ Purple	■ Red	■ Yellow	■ Brown	■ Black	■ Blue

PERFORMANCE PROPERTIES

EN388: 4131	ANSI Cut Level 1					
ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5

BARCODES

ITEM	BAG	DOZEN	CASE
☐ 33-125/XS	----	01616314011863	02616314011863
☐ 33-125/S	----	01616314011870	02616314011870
☐ 33-125/M	----	01616314011887	02616314011887
☐ 33-125/L	----	01616314011894	02616314011894
☐ 33-125/XL	----	01616314011900	02616314011900
☐ 33-125/XXL	----	01616314011917	02616314011917

