



SPECIFICATION SHEET

333-1550



ANSI TYPE R CLASS 3 RIPSTOP SOFTSHELL BLACK BOTTOM FLEECE LINED JACKET

- Tri-laminate ripstop polyester softshell with an inner polyester grid fleece lining and TPU (Thermoplastic polyurethane) membrane
- TPU membrane makes this jacket extremely water resistant, windproof and breathable
- Grid fleece lining reduces fabric weight while increasing warmth and enhances both wicking efficiency and breathability
- 2" segmented reflective material
- Removable fleece lined adjustable hood with zipper attachment
- Two outside chest pockets and two lower hand warmer pockets with waterproof zippers
- Three large inside lower pockets including a computer tablet pocket

APPLICATIONS

- Roadway construction workers
- Survey crews
- Utility workers
- Railway and metro workers
- Emergency response personnel

CARE INSTRUCTIONS

Machine wash cold. No bleach. Tumble dry low. Do not dry clean. Do not iron. This garment may be washed up to 25 cycles.

TECHNICAL DATA

MATERIAL	100% Polyester
CONSTRUCTION	Main: 100% polyester 310g/m ² softshell 75D high elastic double lattice pongee+TPU+160g Lining: 100% polyester fleece Acc: 2" segmented heat transfer reflective tape
COLOR	■ Hi-Vis Lime Yellow
SIZES	S - 5X
PACKAGING	1 per polybag, 10 per case
CASE DIMENSIONS	26" x 17" x 26" / 66cm x 44cm x 22cm
CASE WEIGHT	24 lbs / 11 kgs
COO	China

BARCODES

ITEM	BAG	CASE
■ 333-1550-LY/S	616314214004	02616314214002
■ 333-1550-LY/M	616314214011	02616314214019
■ 333-1550-LY/L	616314214028	02616314214026
■ 333-1550-LY/XL	616314214035	02616314214033
■ 333-1550-LY/2X	616314214042	02616314214040
■ 333-1550-LY/3X	616314214059	02616314214057
■ 333-1550-LY/4X	616314214066	02616314214064
■ 333-1550-LY/5X	616314214073	02616314214071



DIMENSIONS (in/cm)

	S	M	L	XL	2X	3X	4X	5X
A	48 / 122	50 / 126	51 / 130	53 / 134	54 / 138	56 / 142	57 / 146	59 / 150
B	29 / 74	30 / 76	30.7 / 78	31.5 / 80	32 / 82	33 / 84	33.8 / 86	34.6 / 88
C	19.7 / 50	20.5 / 52	21.3 / 54	22 / 56	22.8 / 58	23.6 / 60	24.4 / 62	25.2 / 64
D	25.2 / 64	25.6 / 65	26 / 66	26.4 / 67	26.8 / 68	27.2 / 69	27.6 / 70	28 / 71

