



SPECIFICATION SHEET

34-300



G-TEK® GP™ SEAMLESS KNIT POLYESTER GLOVE WITH NITRILE COATED MICROSURFACE GRIP ON PALM & FINGERS – 13 GAUGE

- Nitrile “MicroSurface” coating provides a superior grip in dry, wet and oily conditions by reacting like tiny suction cups that attach themselves firmly to the material being handled
- Seamless knit polyester shell offers increased comfort, finger dexterity and breathability
- Knit wrist helps prevent dirt and debris from entering the glove
- Breathable back for comfort
- Excellent resistance to liquid permeation
- Oil does not penetrate the glove like foam nitrile styles
- Strong protection from punctures and abrasions

APPLICATIONS

- General assembly of oily parts
- Metal handling
- Fishing
- Machine operation

CARE INSTRUCTIONS

Recommend washing gloves in slightly warm water not exceeding 40°C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Tumble dry on low - maximum temperature 140°F (60°C)

TECHNICAL DATA

MATERIAL	Polyester / Nitrile Coating					
COLOR	Shell: ■ Gray / Coating: ■ Black					
CUFF STYLE	Knit wrist					
SIZES	XS - XXL					
PACKAGING	1 pair per bag, 12 pairs per dozen, 12 dozen per case					
CASE DIMENSIONS	22.4" x 13.8" x 9.8" / 57cm x 35cm x 25cm					
CASE WEIGHT	XS	S	M	L	XL	XXL
	12.3 lbs 5.6 kg	12.8 lbs 5.8 kg	13.4 lbs 6.1 kg	14.3 lbs 6.5 kg	15 lbs 6.8 kg	15.4 lbs 7 kg
COO	China					

PERFORMANCE PROPERTIES

EN388: 4121						
ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5

BARCODES

ITEM	BAG	DOZEN	CASE
■ 34-300/XS	616314214196	01616314214195	02616314214194
■ 34-300/S	616314214172	01616314214171	02616314214170
■ 34-300/M	616314214165	01616314214164	02616314214163
■ 34-300/L	616314214158	01616314214157	02616314214156
■ 34-300/XL	616314214189	01616314214188	02616314214187
■ 34-300/XXL	616314214202	01616314214201	02616314214200



DIMENSIONS (in/cm)

	XS	S	M	L	XL	XXL
A	8.8 / 22.3	9.5 / 24.3	9.6 / 24.4	10 / 25.4	10.5 / 26.6	10.7 / 27.3
B	3.3 / 8.5	3.5 / 9	3.7 / 9.5	3.9 / 10	4.1 / 10.5	4.3 / 11
H	■ Pink	■ Blue	■ Beige	■ Purple	■ Green	■ Gray

Tolerance: ± 0.8 cm (A), ± 0.5 cm (B)

