



SPECIFICATION SHEET

34-876



MAXIFLEX® ULTIMATE™ NYLON / LYCRA® GLOVE WITH NITRILE COATED MICRO-FOAM GRIP

- Ultra cool and very comfortable to wear, breathable coating keeps hands cool and dry
- Excellent dexterity, sensitivity and tactility
- Designed to produce minimal lint and dust;
- Minimal penetration (strike through) keeps the liner soft on the inside of the glove
- CFIA Approved
- Silicone free
- Made from component material which comply with Federal regulations for food contact, 21CFR, 170-199

APPLICATIONS

- General Assembly
- Micro-engineering
- Automotive components
- Painting
- Horticulture

CARE INSTRUCTIONS

Recommend washing gloves in tempered water not exceeding 104° F or 40°C. A mild commercial laundry soap or detergent should be used. Wash in a 5-10 minute cycle time. Rinse in cold water. Tumble dry at temperature not exceeding 104° F or 40° C.

TECHNICAL DATA

MATERIAL	Nylon liner with micro-foam nitrile coating						
COLOR	Shell: ■ Grey / Coating: ■ Black						
CUFF STYLE	Continuous Knit						
SIZES	XXS - XXL						
PACKAGING	12 per dozen, 12 dozen per case						
CASE	22.0" x 14.2" x 7.9" / 56cm x 36cm x 20cm						
CASE WEIGHT	XXS	XS	S	M	L	XL	XXL
	9.4 lbs	14.3 lbs	15.7 lbs	17.0 lbs	18.3 lbs	19.4 lbs	20.7 lbs
	5.3 kg	6.5 kg	7.1 kg	7.7 kg	8.3 kg	8.8 kg	9.4 kg
COO	Sri Lanka						

PERFORMANCE PROPERTIES

EN388: 4131						
ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5

BARCODES

ITEM	BAG	DOZEN	CASE
■ 34-876/XXS	----	01616314027901	02616314027901
■ 34-876/XS	----	01616314011375	02616314011375
■ 34-876/S	----	01616314011382	02616314011382
■ 34-876/M	----	01616314011399	02616314011399
■ 34-876/L	----	01616314011405	02616314011405
■ 34-876/XL	----	01616314011412	02616314011412
■ 34-876/XXL	----	01616314168979	02616314168978



DIMENSIONS (in/cm)

	XXS	XS	S	M	L	XL	XXL
A	7.7 / 18.5	7.9 / 20.0	8.3 / 21.0	8.9 / 22.5	9.1 / 23.0	9.3 / 23.5	9.4 / 24
B	3.0 / 7.5	3.2 / 8.2	3.5 / 8.8	3.5 / 9.0	3.9 / 9.8	4.0 / 10.2	4.1 / 10.4
H	■ Purple	■ Blue	□ White	■ Green	■ Brown	■ Yellow	■ Black

