



# SPECIFICATION SHEET

## 34-900



### MAXIFOAM® LITE™ SEAMLESS KNIT NYLON GLOVE WITH NITRILE COATED FOAM GRIP ON PALM & FINGERS

- Seamless one-piece nylon shell offers increased comfort, finger dexterity and breathability
- Dark coating and gray shell hide dirt
- Light dip for better dexterity, fit and feel
- Extended cuff provides comfort and keeps dirt out
- Made from component materials that comply with Federal Regulations for food contact 21CFR, 170-199
- Silicone-free
- CFIA Approved

### APPLICATIONS

- General Assembly
- Micro-engineering
- Automotive components
- Painting
- Horticulture

### CARE INSTRUCTIONS

Recommend washing gloves in tempered water not exceeding 104° F or 40°C. A mild commercial laundry soap or detergent should be used. Wash in a 5-10 minute cycle time. Rinse in cold water. Tumble dry at temperature not exceeding 104° F or 40° C.

### TECHNICAL DATA

|             |                                              |                    |                    |                    |                    |                    |
|-------------|----------------------------------------------|--------------------|--------------------|--------------------|--------------------|--------------------|
| MATERIAL    | Seamless nylon liner with nitrile coating    |                    |                    |                    |                    |                    |
| COLOR       | Shell: ■ Graphite / Coating: ■ Dark Grey     |                    |                    |                    |                    |                    |
| CUFF STYLE  | Continuous Knit                              |                    |                    |                    |                    |                    |
| SIZES       | XS - XXL                                     |                    |                    |                    |                    |                    |
| PACKAGING   | 12 per dozen, 12 dozen per case              |                    |                    |                    |                    |                    |
| CASE        | 19.7" x 11.6" x 10.6" / 50cm x 29.5cm x 27cm |                    |                    |                    |                    |                    |
| CASE WEIGHT | XS                                           | S                  | M                  | L                  | XL                 | XXL                |
|             | 10.4 lbs<br>4.7 kg                           | 11.0 lbs<br>5.0 kg | 13.0 lbs<br>5.9 kg | 13.7 lbs<br>6.2 kg | 14.3 lbs<br>6.5 kg | 15.4 lbs<br>7.0 kg |
| COO         | Sri Lanka                                    |                    |                    |                    |                    |                    |

### PERFORMANCE PROPERTIES

|             |   |   |   |   |   |   |
|-------------|---|---|---|---|---|---|
| EN388: 3121 |   |   |   |   |   |   |
| ABRASION    | 0 | 1 | 2 | 3 | 4 | 5 |
| CUT         | 0 | 1 | 2 | 3 | 4 | 5 |
| TEAR        | 0 | 1 | 2 | 3 | 4 | 5 |
| PUNCTURE    | 0 | 1 | 2 | 3 | 4 | 5 |

### BARCODES

| ITEM         | BAG  | DOZEN          | CASE           |
|--------------|------|----------------|----------------|
| ■ 34-900/XS  | ---- | 01616314065131 | 02616314065130 |
| ■ 34-900/S   | ---- | 01616314065100 | 02616314065109 |
| ■ 34-900/M   | ---- | 01616314065117 | 02616314065116 |
| ■ 34-900/L   | ---- | 01616314065124 | 02616314065123 |
| ■ 34-900/XL  | ---- | 01616314065148 | 02616314065147 |
| ■ 34-900/XXL | ---- | 01616314153609 | 02616314153608 |



### DIMENSIONS (in/cm)

|          | XS         | S          | M          | L          | XL         | XXL        |
|----------|------------|------------|------------|------------|------------|------------|
| <b>A</b> | 7.0 / 20.0 | 8.3 / 21.0 | 8.7 / 22.0 | 9.1 / 23.0 | 9.4 / 24.0 | 9.6 / 24.5 |
| <b>B</b> | 3.3 / 8.5  | 3.4 / 8.7  | 3.5 / 9.0  | 3.8 / 9.7  | 3.9 / 10.0 | 4.1 / 10.3 |
| <b>H</b> | ■ Blue     | □ White    | ■ Green    | ■ Brown    | ■ Yellow   | ■ Black    |

