



# SPECIFICATION SHEET

## 34-9025



### MAXIFLEX® COMFORT™ SEAMLESS KNIT COTTON / NYLON / LYCRA® GLOVE WITH NITRILE COATED MICRO-FOAM GRIP

- MaxiFlex® Comfort by ATG®, cobalt blue micro-foam nitrile coated palm, full finger and knuckles, seamless gray cotton/nylon/Lycra liner
- Cotton/nylon/Lycra® blend is more comfortable, breathable and launderable than nylon and assists with perspiration management
- 3/4 dip protects back of fingers yet allows glove to breathe
- Cobalt blue coating and gray shell hide dirt
- Extended cuff provides comfort and keeps dirt out
- Made from component materials that comply with Federal Regulations for food contact 21CFR, 170-199
- Treated with Actifresh® to impede odors and eliminate germs
- Silicone-free
- CFIA Approved

### APPLICATIONS

- General Assembly
- Micro-engineering
- Automotive components
- Painting
- Horticulture

### CARE INSTRUCTIONS

Recommend washing gloves in tempered water not exceeding 104° F or 40°C. A mild commercial laundry soap or detergent should be used. Wash in a 5-10 minute cycle time. Rinse in cold water. Tumble dry at temperature not exceeding 104° F or 40° C.

### TECHNICAL DATA

|            |                                                                                            |                 |                 |                 |                 |
|------------|--------------------------------------------------------------------------------------------|-----------------|-----------------|-----------------|-----------------|
| MATERIAL   | Nitrile, nylon, cotton, Lycra®                                                             |                 |                 |                 |                 |
| COLOR      | Shell: <span style="color: grey;">■</span> Grey / <span style="color: blue;">■</span> Blue |                 |                 |                 |                 |
| CUFF STYLE | Knitwrist                                                                                  |                 |                 |                 |                 |
| SIZES      | XS - XL                                                                                    |                 |                 |                 |                 |
| PACKAGING  | 12 per dozen, 12 dozen per case                                                            |                 |                 |                 |                 |
| CASE       | 19.7" x 11.6" x 10.6" / 50cm x 29.5cm x 27cm                                               |                 |                 |                 |                 |
| CASE       | XS                                                                                         | S               | M               | L               | XL              |
| WEIGHT     | 14.3lbs / 6.5kg                                                                            | 16.3lbs / 7.4kg | 18.3lbs / 8.3kg | 19.4lbs / 8.8kg | 20.0lbs / 9.1kg |
| COO        | Sri Lanka                                                                                  |                 |                 |                 |                 |

### PERFORMANCE PROPERTIES

|             |   |   |   |   |   |   |
|-------------|---|---|---|---|---|---|
| EN388: 3121 |   |   |   |   |   |   |
| ABRASION    | 0 | 1 | 2 | 3 | 4 | 5 |
| CUT         | 0 | 1 | 2 | 3 | 4 | 5 |
| TEAR        | 0 | 1 | 2 | 3 | 4 | 5 |
| PUNCTURE    | 0 | 1 | 2 | 3 | 4 | 5 |

### BARCODES

| ITEM         | BAG | DOZEN          | CASE           |
|--------------|-----|----------------|----------------|
| ■ 34-9025/XS | --- | 01616314031144 | 02616314031144 |
| ■ 34-9025/S  | --- | 01616314031120 | 02616314031120 |
| ■ 34-9025/M  | --- | 01616314031113 | 02616314031113 |
| ■ 34-9025/L  | --- | 01616314031106 | 02616314031106 |
| ■ 34-9025/XL | --- | 01616314031137 | 02616314031137 |



### DIMENSIONS (in/cm)

|          | XS                                       | S                                          | M                                          | L                                          | XL                                           |
|----------|------------------------------------------|--------------------------------------------|--------------------------------------------|--------------------------------------------|----------------------------------------------|
| <b>A</b> | 7.1 / 18.0                               | 7.7 / 19.5                                 | 8.3 / 21.0                                 | 8.7 / 22.0                                 | 9.1 / 23.0                                   |
| <b>B</b> | 3.2 / 8.2                                | 3.5 / 9.0                                  | 3.7 / 9.4                                  | 3.9 / 9.8                                  | 4.0 / 10.2                                   |
| <b>H</b> | <span style="color: blue;">■</span> Blue | <span style="color: white;">■</span> White | <span style="color: green;">■</span> Green | <span style="color: brown;">■</span> Brown | <span style="color: yellow;">■</span> Yellow |

