



SPECIFICATION SHEET

34-C229



G-TEK® BN, KNIT NYLON GLOVE WITH NITRILE COATED SMOOTH GRIP

- Seamless one-piece nylon shell offers increased comfort, finger dexterity and breathability
- Solid dipped nitrile coatings provide excellent dry grip and will not absorb liquids into the coating
- Knit wrist helps prevent dirt and debris from entering the glove

APPLICATIONS

- Assembly
- Construction
- Inspection
- Material handling
- Refuse handling
- Landscaping
- Gardening

CARE INSTRUCTIONS

Recommend washing gloves in slightly warm water not exceeding 40°C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Hang dry; tumble dry on low - maximum temperature 60°C

PERFORMANCE PROPERTIES

EN388: 4131						
ABRASION	0	1	2	3	4	-
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	-
PUNCTURE	0	1	2	3	4	-

TECHNICAL DATA

MATERIAL	Seamless Nylon
COLOR	Shell: ☐ White / Coating: ☒ Blue
CUFF STYLE	Continuous knit
SIZES	S - XL
PACKAGING	12 pair per dozen; 25 dozen per case
CASE DIMENSIONS	Small: 64cm x 27cm x 47cm / 25.2" x 10.6" x 18.5"
	Medium: 66cm x 28cm x 47cm / 26" x 11" x 18.5"
	Large: 66cm x 29cm x 47cm / 26" x 11.4" x 18.5"
	X-Large: 66cm x 29cm x 47cm / 26" x 11.4" x 18.5"
CASE WEIGHT	Small: 12 kg / 26.5 lbs
	Medium: 15 kg / 33 lbs
	Large: 15.5 kg / 34.25 lbs
	X-Large: 16 kg / 35.25 lbs
COO	China

BARCODES

ITEM	PAIR	DOZEN	CASE
☒ 34-C229 / S	616314018220	01616314018220	02616314018220
☒ 34-C229 / M	616314018237	01616314018237	02616314018237
☒ 34-C229 / L	616314018244	01616314018244	02616314018244
☒ 34-C229 / XL	616314018251	01616314018251	02616314018251



DIMENSIONS (in/cm)

	S	M	L	XL
A	8.9 / 22.5	9.4 / 24	9.8 / 25	10.2 / 26
B	3.3 / 8.5	3.5 / 9	3.7 / 9.5	3.9 / 10
H	☐ White	☒ Green	☒ Brown	☐ Yellow

