



# SPECIFICATION SHEET

## 34-C232



### G-TEK® SEAMLESS KNIT NYLON GLOVE WITH NITRILE COATED FOAM GRIP ON PALM & FINGERS - ECONOMY GRADE

- Seamless one-piece nylon shell offers increased comfort, finger dexterity and breathability
- Foam Nitrile coatings are compatible with light oils and will provide a good grip and excellent abrasion resistance
- Knit Wrist helps prevent dirt and debris from entering the glove

### APPLICATIONS

- Manufacturing and assembly applications where abrasion, cut and puncture resistance is required

### CARE INSTRUCTIONS

Recommend washing gloves in slightly warm water not exceeding 40° C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Tumble dry on low - maximum temperature 140°F (60° C).

### TECHNICAL DATA

MATERIAL	Seamless nylon with foam nitrile coating on palm and fingers				
COLOR	Shell: ■ Grey / ■ Black				
CUFF STYLE	Continuous knit				
SIZES	XS - XL				
PACKAGING	12 per dozen, 25 dozen per case				
CASE	19.7" x 11.6" x 10.6" / 60cm x 28cm x 47cm				
CASE WEIGHT	XS	S	M	L	XL
	26.2 lbs 11.9 kg	29.8 lbs 13.5 kg	32.0 lbs 14.5 kg	34.2 lbs 15.5 kg	36.3 lbs 16.5 kg
COO	China				



### DIMENSIONS (in/cm)

	XS	S	M	L	XL
A	8.6 / 22	9.1 / 23	9.4 / 24	9.8 / 25	10.2 / 26
B	3.7 / 9.5	4.1 / 10.5	4.3 / 10.8	4.4 / 11.2	4.5 / 11.5
H	Blue	White	Green	Brown	Yellow

### PERFORMANCE PROPERTIES

EN388: 4121						
ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5

### BARCODES

ITEM	BAG	DOZEN	CASE
■ 34-C232/XS	---	01616314017896	02616314017896
■ 34-C232/S	---	01616314017902	02616314017902
■ 34-C232/M	---	01616314017919	02616314017919
■ 34-C232/L	---	01616314017926	02616314017926
■ 34-C232/XL	---	01616314017933	02616314017933

