



SPECIFICATION SHEET

364-ML2FMP

2-LAYER COTTON TWILL / FLEECE WINTER LINER WITH MOUTHPIECE AND FR TREATED OUTER SHELL - MID LENGTH

- Mid-length
- 2 Layers
- Cotton Twill/Fleece
- FR treated cotton, up to 30 washes

APPLICATIONS

- Cold working conditions
- Construction
- Woodworking
- Refineries
- Oil drilling
- Maintenance
- Mining

CARE INSTRUCTIONS

FR treated: 30 washes.

TECHNICAL DATA

MATERIAL	Main fabric - 10x10/80x46 100% cotton twill FR Lining - 260gsm 100% poly fleece
COLOR	■ Navy Blue
SIZES	One Size Fits Most
PACKAGING	1 per polybag; 6 per bag; 72 per case
CASE (IN/CM)	20 x 14.5 x 13 / 50.8 x 36.8 x 33
CASE WEIGHT	18 lbs /8.2 kg
COO	China

BARCODES

ITEM	EACH	BAG	CASE
■ 364-ML2FMP	---	01616314100795	02616314100794



DIMENSIONS (in/cm)

	OSFM				
A	6.7 / 17	---	---	---	---
B	11 / 28	---	---	---	---

