



# SPECIFICATION SHEET

## 38-720

### SEAMLESS KNIT COTTON / POLYESTER GLOVE WITH DOUBLE-SIDED EVERGRIP™ NITRILE COATING

- Seamless cotton/polyester knit shell is comfortable and flexible
- Knit Wrist helps prevent dirt and debris from entering the glove
- Double-sided Nitrile “MW” pattern provides superior grip and abrasion resistance compared to rubber or PVC coatings
- Coated with a special formulated nitrile to resist melting
- Curved finger style provides an ergonomic, comfortable fit
- Made from component materials which comply with Federal regulations for food contact 21 CFR 170-199
- Launderable for extended life and to reduced replacement costs

### APPLICATIONS

- Automotive Plants
- Material Handling
- General Maintenance
- Packaging
- Construction
- Parts Handling
- Warehousing
- Plywood Industry
- Glass Handling

### CARE INSTRUCTIONS

Recommend washing gloves in slightly warm water not exceeding 40° C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Hang dry; tumble dry is not recommended.

### TECHNICAL DATA

MATERIAL	Cotton / Nitrile
COLOR	Liner: Natural / Coating: Rust
CUFF STYLE	Continuous Knit
SIZES	S - L
PACKAGING	12 pairs per dozen, 24 dozen per case
CASE DIMENSIONS	20.0" x 20.0" x 16.0" / 50.8cm x 50.8cm x 40.6cm
CASE WEIGHT	69.6 lbs / 31.5 kg
COO	United States of America

### BARCODES

ITEM	DOZEN	CASE
38-720/S	01616314018336	02616314018336
38-720/M	01616314032677	02616314032677
38-720/L	01616314018343	02616314018343



### DIMENSIONS (in/cm)

	S	M	L
A	8.9 / 22.5	9.4 / 24.0	10.0 / 25.5
B	3.7 / 9.5	3.9 / 10.0	4.1 / 10.5

