



SPECIFICATION SHEET

39-C1305



G-TEK® SEAMLESS KNIT COTTON/ POLYESTER GLOVE WITH LATEX COATED CRINKLE GRIP ON PALM & FINGERS - REGULAR GRADE

- Latex "Crinkle" coating provides superior grip in wet and dry conditions
- Knit Wrist helps prevent dirt and debris from entering the glove
- Seamless cotton/polyester knit shell is comfortable and flexible
- Ergonomic shaped curved finger pattern
- Breathable back for comfort

APPLICATIONS

- Assembly
- Construction
- Inspection
- Material handling
- Refuse handling
- Landscaping and gardening

CARE INSTRUCTIONS

Recommend washing gloves in slightly warm water not exceeding 40°C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Tumble dry on low - maximum temperature 140°F (60°C)

TECHNICAL DATA

MATERIAL	65% Polyester / 35% Cotton				
COLOR	Shell: ■ Gray / Coating: ■ Blue				
CUFF STYLE	Continuous Knit				
SIZES	XS - XL				
PACKAGING	12 pairs per dozen, 6 dozen per case				
CASE	8.3" x 11" x 27.5" / 70cm x 28cm x 21cm				
CASE WEIGHT	XS	S	M	L	XL
	14.3 lbs 6.5 kg	15.4 lbs 7 kg	16.5 lbs 7.5 kg	17.6 lbs 8 kg	18.7 lbs 8.5 kg
COO	China				

PERFORMANCE PROPERTIES

EN388: 2242						
ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5

BARCODES

ITEM	BAG	DOZEN	CASE
■ 39-C1305/XS	----	01616314046529	02616314046528
■ 39-C1305/S	----	01616314046536	02616314046535
■ 39-C1305/M	----	01616314046543	02616314046542
■ 39-C1305/L	----	01616314046550	02616314046559
■ 39-C1305/XL	----	01616314046567	02616314046566



DIMENSIONS (in/cm)

	XS	S	M	L	XL
A	9.2 / 23.5	9.4 / 24	10 / 25.5	10.2 / 26	11 / 28
B	3.5 / 9	3.8 / 9.7	3.9 / 10	4.1 / 10.5	4.3 / 11
H	■ Yellow	■ Green	■ Blue	■ Brown	■ Gray

