



SPECIFICATION SHEET

40-6411



CLEANTEAM® KNIT NYLON / CARBON FIBER ELECTROSTATIC DISSIPATIVE (ESD) GLOVE WITH PVC DOT GRIP

- Electrostatic Dissipative (ESD) fiber yarns blended with low lint nylon which reduces static build-up on the glove surface for improved performance in electronics assembly
- Seamless knit gloves provide great dexterity
- PVC dots provide enhanced grip and extra cut and abrasion resistance
- 15 gauge

APPLICATIONS

- Circuit board manufacturing
- Munitions
- Electronics assembly
- Aerospace

CARE INSTRUCTIONS

ESD Gloves can't be washed more than 2 times. Hand wash in normal temperature water (not exceeding 30° C) with a mild soap or detergent. Wash for 3-5 minutes, and rinse in cold water. Hang dry. Do not use a washing machine or tumble dry. Do not use softener or bleach.

TECHNICAL DATA

MATERIAL	Nylon / Carbon Fiber / PVC
COLOR	<input type="checkbox"/> White
CUFF STYLE	Continuous Knit
SIZES	S & L
PACKAGING	12 pairs per dozen, 25 dozen per case
CASE SIZE	S: 39cm x 20cm x 50cm / 15.4" x 7.9" x 19.7" L: 39cm x 23cm x 50cm / 15.4" x 9.1" x 19.7"
CASE WEIGHT	S: 23.1 lbs / 10.5 kg L: 24.3 lbs / 11 kg
COO	Korea



DIMENSIONS (in/cm)

	S	L	---	---	---
A	7.9 / 20	8.7 / 22	---	---	---
B	3.5 / 9	3.8 / 9.6	---	---	---
H	<input type="checkbox"/> Orange	<input type="checkbox"/> Blue	---	---	---

Tolerance: +/-0.5 cm

PERFORMANCE PROPERTIES

EN388: 4131						
ABRASION	0	1	2	3	4	-
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	-
PUNCTURE	0	1	2	3	4	-

- Electrical Surface Resistivity (ASTM D 257:2007): Below 7.5 x 10⁷
- Test Condition: (20+/-2)°C, (65+/-5)% R.H.
- Applied Voltage: 500V, 60s

BARCODES

ITEM	BAG	DOZEN	CASE
<input type="checkbox"/> 40-6411/S	---	01616314001086	02616314001086
<input type="checkbox"/> 40-6411/L	---	01616314001079	02616314001079

