



# SPECIFICATION SHEET

## 40-732

### CLEANTEAM® MEDIUM WEIGHT SEAMLESS KNIT NYLON CLEAN ENVIRONMENT GLOVE - HALF-FINGER

- Seamless nylon knit shell is comfortable and reduces hand fatigue
- Knit Wrist helps prevent dirt and debris from entering the glove
- Reversible design allows replacing one glove at a time, rather than pairs
- Nylon yarns absorb perspiration and leave hands cool and comfortable
- Half-Finger design provides excellent dexterity
- Ideal for use where low lint properties are desired
- Can be used as a glove liner
- Color coded hems for easy size identification

### APPLICATIONS

- Product handling, finishing and assembly
- Electronics assembly
- Photography labs
- Computer manufacturing

### CARE INSTRUCTIONS

Recommend washing gloves in slightly warm water not exceeding 40°C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Tumble dry on low - maximum temperature 140°F (60°C)

### TECHNICAL DATA

MATERIAL	100% nylon			
COLOR	□ White			
CUFF STYLE	Knit Wrist			
SIZES	S - XL			
PACKAGING	12 pair per dozen; 25 dozen per case			
CASE (IN/CM)	(S) 21.3 x 6.7 x 15 / 54 x 17 x 38 (M) 21.7 x 7.5 x 15 / 55 x 19 x 38 (L) 22.4 x 7.9 x 15.7 / 57 x 20 x 40 (XL) 23.2 x 8.3 x 15 / 59 x 21 x 38			
CASE WEIGHT	S	M	L	XL
	14 lbs / 6.4 kg	14 lbs / 6.4 kg	14.75 lbs / 6.7 kg	18.25 lbs / 8.3 kg
COO	China			

### BARCODES

ITEM	BAG	DOZEN	CASE
□ 40-732/S	---	01616314001291	02616314001291
□ 40-732/M	---	01616314001307	02616314001307
□ 40-732/L	---	01616314001314	02616314001314
□ 40-732/XL	---	01616314001321	02616314001321



### DIMENSIONS (in/cm)

	S	M	L	XL
A	6.5 / 16.5	6.9 / 17.6	7.3 / 18.5	8 / 20.3
B	3.3 / 8.3	3.3 / 8.3	3.4 / 8.6	3.7 / 9.5
H	Green	Orange	Blue	Gray

Tolerance: +/- 0.2 cm

