



SPECIFICATION SHEET

41-1405



POWERGRAB™ THERMO HI-VIS SEAMLESS KNIT ACRYLIC TERRY GLOVE WITH LATEX MICROFINISH® GRIP

- Seamless construction for comfortable fit
- 10 gauge
- Excellent thermal insulation
- Quickly evaporates moisture from the skin
- Extra softness for non-chafing comfort
- Excellent launderability characteristics

APPLICATIONS

- Used in refrigerated areas
- Utilities
- Food Processing
- Commercial Fishing
- Construction
- Outdoor winter activities and recreation

CARE INSTRUCTIONS

Recommend washing gloves in slightly warm water not exceeding 40°C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Hang dry; tumble dry is not recommended.

TECHNICAL DATA

MATERIAL	Acrylic terry liner and MicroFinish™ latex				
COLOR	Shell: ■ Lime Yellow / Coating: ■ Brown				
CUFF STYLE	Continuous knit				
SIZES	S - XXL				
PACKAGING	12 per dozen, 6 dozen per case				
CASE	27.2" x 10.6" x 11.4" / 69cm x 26.8cm x 29cm				
CASE WEIGHT	S	M	L	XL	XXL
	15.0 lbs 6.8 kg	15.4 lbs 7.0 kg	16.3 lbs 7.4 kg	17.9 lbs 8.1 kg	19.6 lbs 8.9 kg
COO	China				

PERFORMANCE PROPERTIES

EN388: 2231						
ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5

BARCODES

ITEM	PR	DOZEN	CASE
■ 41-1405/S	616314179501	01616314179500	02616314179509
■ 41-1405/M	616314179495	01616314179494	02616314179493
■ 41-1405/L	616314179488	01616314179487	02616314179486
■ 41-1405/XL	616314179518	01616314179517	02616314179516
■ 41-1405/XXL	616314179525	01616314179524	02616314179523



DIMENSIONS (in/cm)

	S	M	L	XL	XXL
A	9.8 / 25	10 / 25.5	10.2 / 26	10.8 / 27.5	11 / 28
B	3.9 / 9.8	4 / 10.1	4.1 / 10.5	4.4 / 11.2	4.5 / 11.5
H	■ Green	■ Blue	■ Tan	■ Gray	■ Purple

