



# SPECIFICATION SHEET

## 41-1475



### POWERGRAB™ THERMO HI-VIS SEAMLESS KNIT ACRYLIC TERRY GLOVE WITH LATEX MICROFINISH® GRIP

- Seamless construction for comfortable fit
- Excellent thermal insulation
- Quickly evaporates moisture from the skin
- Extra softness for non-chafing comfort
- Excellent launderability characteristics

#### APPLICATIONS

- Used in refrigerated areas
- Utilities
- Food Processing
- Commercial Fishing
- Construction
- Outdoor winter activities and recreation

#### CARE INSTRUCTIONS

Recommend washing gloves in slightly warm water not exceeding 40°C. A mild non-ionic detergent should be used. A 5-10 minute cycle time should be employed. Hang dry; tumble dry is not recommended.

#### TECHNICAL DATA

|             |                                                                                                           |          |          |          |          |
|-------------|-----------------------------------------------------------------------------------------------------------|----------|----------|----------|----------|
| MATERIAL    | Acrylic terry liner and MicroFinish™ latex                                                                |          |          |          |          |
| COLOR       | Shell: <span style="color: orange;">■</span> Orange / Coating: <span style="color: brown;">■</span> Brown |          |          |          |          |
| CUFF STYLE  | Continuous knit                                                                                           |          |          |          |          |
| SIZES       | S - XXL                                                                                                   |          |          |          |          |
| PACKAGING   | 12 per dozen, 6 dozen per case                                                                            |          |          |          |          |
| CASE        | 27.2" x 10.6" x 11.4" / 69cm x 26.8cm x 29cm                                                              |          |          |          |          |
| CASE WEIGHT | S                                                                                                         | M        | L        | XL       | XXL      |
|             | 16.8 lbs                                                                                                  | 18.1 lbs | 18.5 lbs | 20.1 lbs | 21.0 lbs |
|             | 7.6 kg                                                                                                    | 8.2 kg   | 8.4 kg   | 9.1 kg   | 9.5 kg   |
| COO         | China                                                                                                     |          |          |          |          |

#### PERFORMANCE PROPERTIES

|             |   |   |   |   |   |   |
|-------------|---|---|---|---|---|---|
| EN388: 2121 |   |   |   |   |   |   |
| ABRASION    | 0 | 1 | 2 | 3 | 4 | 5 |
| CUT         | 0 | 1 | 2 | 3 | 4 | 5 |
| TEAR        | 0 | 1 | 2 | 3 | 4 | 5 |
| PUNCTURE    | 0 | 1 | 2 | 3 | 4 | 5 |

#### BARCODES

| ITEM                                              | BAG | DOZEN          | CASE           |
|---------------------------------------------------|-----|----------------|----------------|
| <span style="color: orange;">■</span> 41-1475/S   | --- | 01616314125156 | 01616314125155 |
| <span style="color: orange;">■</span> 41-1475/M   | --- | 01616314125163 | 01616314125162 |
| <span style="color: orange;">■</span> 41-1475/L   | --- | 01616314125170 | 01616314125179 |
| <span style="color: orange;">■</span> 41-1475/XL  | --- | 01616314125187 | 01616314125186 |
| <span style="color: orange;">■</span> 41-1475/XXL | --- | 01616314125194 | 01616314125193 |



#### DIMENSIONS (in/cm)

|          | S                                          | M                                        | L                                        | XL                                       | XXL                                          |
|----------|--------------------------------------------|------------------------------------------|------------------------------------------|------------------------------------------|----------------------------------------------|
| <b>A</b> | 9.8 / 25                                   | 10 / 25.5                                | 10.2 / 26                                | 10.8 / 27.5                              | 11 / 28                                      |
| <b>B</b> | 3.9 / 9.8                                  | 4 / 10.1                                 | 4.1 / 10.5                               | 4.4 / 11.2                               | 4.5 / 11.5                                   |
| <b>H</b> | <span style="color: green;">■</span> Green | <span style="color: blue;">■</span> Blue | <span style="color: brown;">■</span> Tan | <span style="color: gray;">■</span> Gray | <span style="color: purple;">■</span> Purple |

