



# SPECIFICATION SHEET

## 48-L162Y



### ASSURANCE® UNSUPPORTED LATEX, FLOCK LINED WITH HONEYCOMB GRIP - 16 MIL

- Provides resistance to acids, alkalis, alcohols, salts, ketones, and animal fats
- Flock lining provides increased comfort and ease of donning
- Honeycomb pattern for an enhanced grip
- Rolled cuff adds additional strength to cuff edge for longer glove life and prevents liquid run-off
- Pair packed for ease of distribution
- Made from component materials which comply with FDA regulations for food contact. 21CFR, 170-199
- CFIA Approved

### APPLICATIONS

- Janitorial
- Sanitation
- General maintenance

### CARE INSTRUCTIONS

It is strongly advised to not wash and re-use these gloves when they are used to protect against chemical products

### TECHNICAL DATA

MATERIAL	Natural rubber latex
COLOR	Yellow
CUFF STYLE	Rolled cuff
SIZES	S - XL
PACKAGING	12 pairs per bag, 12 bags per case
CASE	12.6" x 10.9" x 12.5" / 32cm x 27.6cm x 31.8cm
CASE WEIGHT	17.6 lbs / 3.7 kg
COO	Malaysia

### PERFORMANCE PROPERTIES

EN388: 1010						
ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5

### ELONGATION INFORMATION

BEFORE AGING		AFTER ACCELERATED AGING	
Tensile Strength (minimum)	Elongation (minimum)	Tensile Strength (minimum)	Elongation (minimum)
(Mpa)	%	(Mpa)	%
10	500	75	375



### BARCODES

ITEM	PAIR	DOZEN	CASE
48-L162Y/XL	616314035159	01616314035159	02616314035159
48-L162Y/L	616314035128	01616314035128	02616314035128
48-L162Y/M	616314035135	01616314035135	02616314035135
48-L162Y/S	616314035142	01616314035142	02616314035142

### DIMENSIONS (in/cm)

	S	M	L	XL
A	12.0 / 30.5	12.0 / 30.5	12.0 / 30.5	12.0 / 30.5
B	3.5 / 9.0	3.9 / 10.0	4.3 / 10.8	4.6 / 11.6
Palm Thickness: 0.40mm				
Cuff Thickness: 0.35mm				
Finger Tip Thickness: 0.43mm				

