



SPECIFICATION SHEET

48-L212Y



ASSURANCE[®] UNSUPPORTED LATEX, INDUSTRIAL FLOCK LINED WITH RAISED DIAMOND GRIP - 21 MIL

- Provides resistance to acids, alkalis, alcohols, salts, ketones and animal fats; chlorinated
- Flock lining provides increased comfort and ease of donning
- Rolled cuff adds additional strength to cuff edge for longer glove life and prevents liquid run-off
- Made from component materials which comply with Federal regulations for food contact. 21CFR, 170-199
- CFIA Approved

APPLICATIONS

- Janitorial
- Sanitation
- General maintenance

CARE INSTRUCTIONS

It is strongly advised to not wash and re-use these gloves when they are used to protect against chemical products

TECHNICAL DATA

MATERIAL	Natural rubber latex, cotton				
COLOR	Yellow				
CUFF STYLE	Rolled bead				
SIZES	XS - XL				
PACKAGING	12 per dozen, 12 dozen per case				
CASE	16.9" x 9.8" x 14.2" / 43cm x 25cm x 36cm				
CASE WEIGHT	XS	S	M	L	XL
	20.0 lbs 9.1 kg	21.3 lbs 9.3 kg	22.9 lbs 10.4 kg	25.4 lbs 11.5 kg	28.6 lbs 13.0 kg
COO	Malaysia				

PERFORMANCE PROPERTIES

EN388: 1020						
ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5

BARCODES

ITEM	BAG	DOZEN	CASE
48-L212Y/XS	----	01616314038259	02616314038259
48-L212Y/S	----	01616314034701	02616314034701
48-L212Y/M	----	01616314034695	02616314034695
48-L212Y/L	----	01616314034688	02616314034688
48-L212Y/XL	----	01616314034718	02616314034718



DIMENSIONS (in/cm)

	XS	S	M	L	XL
A	11.8 / 30.0	11.8 / 30.0	11.8 / 30.0	11.8 / 30.0	11.8 / 30.0
B	3.7 / 9.5	3.9 / 10.0	4.1 / 10.5	4.4 / 11.3	4.8 / 12.1
Palm Thickness: 0.52mm ± 0.05mm					
Tolerance (length) " ± 10mm					

