



SPECIFICATION SHEET

50-N150G



ASSURANCE® UNSUPPORTED NITRILE, FLOCK LINED WITH RAISED DIAMOND GRIP - 15 MIL

- Medium weight construction and hand specific design provide real comfort with protection
- Provides flexibility, tactile sensitivity and dexterity sometimes lacking in heavier gauge unsupported nitriles
- Provides the protection from chemical and physical hazards not always found in thinner gauge nitrile disposables
- Flock lining provides increased comfort and ease of donning
- Straight cuff adds additional length to protect the forearm from liquid run-off
- Raised Diamond pattern for an enhanced grip
- Chlorinated to harden and cleanse the surface of the glove
- Made from component materials which comply with Federal regulations for food contact. 21 CFR, 170-199

APPLICATIONS

- Light chemical applications
- Printing
- Meat and poultry processing

TECHNICAL DATA

MATERIAL	Nitrile				
COLOR	Green				
CUFF STYLE	Straight Cuff				
SIZES	S- XXL				
PACKAGING	12 pairs per dozen, 12 dozen per case				
CASE	14.6" x 13" x 9.4" / 37cm x 33cm x 24cm				
CASE WEIGHT	S	M	L	XL	XXL
	14 lbs 6.4 kgs	14.2 lbs 6.3 kgs	14.4 lbs 6.5 kgs	14.6 lbs 6.6 kgs	14.8 lbs 6.7 kgs
COO	China				

PERFORMANCE PROPERTIES

EN388: 3101						
ABRASION	0	1	2	3	4	-
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	-
PUNCTURE	0	1	2	3	4	-

BARCODES

ITEM	PAIR	DOZEN	CASE
50-N150G/S	616314206207	01616314206206	02616314206205
50-N150G/M	616314206191	01616314206190	02616314206199
50-N150G/L	616314206184	01616314206183	02616314206182
50-N150G/XL	616314206214	01616314206213	02616314206212
50-N150G/XXL	616314206221	01616314206220	02616314206229



DIMENSIONS (in/cm)

	S	M	L	XL	XXL
A	13 / 33	13 / 33	13 / 33	13 / 33	13 / 33
B	2.7 / 6.8	2.8 / 7	3.1 / 7.8	3.3 / 8.5	3.5 / 8.8

Thickness: 0.38 mm

