




SPECIFICATION SHEET

50-N160G



ASSURANCE® UNSUPPORTED NITRILE, FLOCK LINED WITH RAISED DIAMOND GRIP - 15 MIL

- Light weight construction and hand specific design provide real comfort with protection
- Provides flexibility, tactile sensitivity and dexterity sometimes lacking in heavier gauge unsupported nitriles
- Provides the protection from chemical and physical hazards not always found in thinner gauge nitrile disposables
- Raised diamond grip pattern provides excellent grip
- Made from component materials that comply with Federal Regulations for food contact 21CFR, 170-199
- CFIA Approved

APPLICATIONS

- Light chemical applications
- Printing
- Meat and poultry processing

TECHNICAL DATA

MATERIAL	Nitrile, cotton					
COLOR	Green					
CUFF STYLE	Straight Cuff					
SIZES	XS- XXL					
PACKAGING	12 pairs per dozen, 12 dozen per case					
CASE	14.2" x 11.4" x 11.4" / 36cm x 29cm x 29cm					
CASE WEIGHT	XS	S	M	L	XL	XXL
	19.4 lbs 8.8 kg	20.4 lbs 9.3 kg	21.6 lbs 9.8 kg	22.6 lbs 10.3 kg	24.2 lbs 11.0 kg	26.0 lbs 11.8 kg
COO	Sri Lanka					

PERFORMANCE PROPERTIES

EN388: 4101							
ABRASION	0	1	2	3	4	-	
CUT	0	1	2	3	4	5	
TEAR	0	1	2	3	4	-	
PUNCTURE	0	1	2	3	4	-	

BARCODES

ITEM	BAG	DOZEN	CASE
50-N160G/XS	---	01616314038006	02616314038006
50-N160G/S	---	01616314035753	02616314035753
50-N160G/M	---	01616314035746	02616314035746
50-N160G/L	---	01616314035739	02616314035739
50-N160G/XL	---	01616314035760	02616314035760
50-N160G/XXL	---	01616314035777	02616314035777



DIMENSIONS (in/cm)

	XS	S	M	L	XL	XXL
A	13.0 / 33.0	13.0 / 33.0	13.0 / 33.0	13.0 / 33.0	13.0 / 33.0	13.0 / 33.0
B	2.4 / 6.2	2.7 / 6.8	2.8 / 7.0	3.1 / 7.8	3.3 / 8.5	3.5 / 8.8
Thickness: 0.38 mm						

