



SPECIFICATION SHEET

56-AG566



ACTIVGRIP™ NITRILE COATED GLOVE WITH COTTON LINER AND MICROFINISH GRIP - 12"G

- Features a revolutionary surface treatment that provides a superior grip in dry, wet and oily conditions
- MicroFinish™ adjusts to different conditions by reacting like tiny suction cups
- Seamless cotton liner for comfort and better fit
- MicroFinish™ coating provides excellent resistance to liquid permeation
- Tremendous comfort and dexterity
- Strong protection to punctures and abrasions

APPLICATIONS

- General assembly of oily parts
- Metal handling
- Fishing
- Machine operation

CARE INSTRUCTIONS

Wash using warm water; neutral detergent. Water temperature not to exceed 50°C/122°F. Hang dry or dry on low heat.

TECHNICAL DATA

MATERIAL	Cotton/polyester, nitrile			
CONSTRUCTION	Nitrile coated 13 gauge seamless cotton/polyester liner			
COLOR	■ Green			
CUFF STYLE	Open Cuff			
SIZES	S - XL			
PACKAGING	12 pairs per dozen, 6 dozen per case			
CASE	16.1" x 13.2" x 11.6" / 41cm x 33.5cm x 29.5cm			
CASE WEIGHT (S-XL)	S	M	L	XL
	17.2 lbs 7.8 kg	17.8 lbs 8.1 kg	18.7 lbs 8.5 kg	20.5 lbs 9.3 kg
COO	China			
HARM CODE	6116.10.6500			

PERFORMANCE PROPERTIES

EN388: 4121						
ABRASION	0	1	2	3	4	-
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	-
PUNCTURE	0	1	2	3	4	-

BARCODES

ITEM	BAG	DOZEN	CASE
■ 56-AG566/S	---	01616314014185	02616314014185
■ 56-AG566/M	---	01616314014192	02616314014192
■ 56-AG566/L	---	01616314014208	02616314014208
■ 56-AG566/XL	---	01616314014215	02616314014215



DIMENSIONS (in/cm)

	S	M	L	XL
A	11.8 / 30	11.8 / 30	11.8 / 30	11.8 / 30
B	4.1 / 10.5	4.5 / 11.1	4.7 / 12.0	4.9 / 12.5

