



SPECIFICATION SHEET

63-532

AMBI-DEX® AXLE DISPOSABLE NITRILE GLOVE, POWDERED WITH TEXTURED GRIP - 4 MIL BLUE

- Economical puncture resistance with great comfort, dexterity and tactile sensitivity
- Textured grip provides a good grip in wet or dry environments
- Ambidexterous and powdered for quick and easy donning
- Contains no natural rubber latex proteins
- Beaded cuff
- Complies with FDA food handling requirements (21 CFR 177.2600)
- CFIA approved
- AQL 4.0

APPLICATIONS

- Liquids
- General maintenance
- Food processing

TECHNICAL DATA

MATERIAL	Nitrile				
POWDER	Cornstarch				
COLOR	Blue				
CUFF STYLE	Rolled beaded				
SIZES	S - XXL				
PACKAGING	100 gloves per dispenser box; 10 boxes per case (1,000 gloves)				
CASE	14.1" x 10.2" x 9.6" / 36cm x 26cm x 24.5cm				
CASE WEIGHT	S	M	L	XL	XXL
	11.5 lbs 5.2 kg	12.3 lbs 5.6 kg	13.4 lbs 6.1 kg	14.6 lbs 6.6 kg	15.8 lbs 7.2 kg
COO	Malaysia				

ELONGATION INFORMATION

BEFORE AGING		AFTER ACCELERATED AGING	
Tensile Strength (minimum) (Mpa)	Elongation (minimum) (%)	Tensile Strength (minimum) (Mpa)	Elongation (minimum) (%)
14	500	14	400

BARCODES

ITEM	BAG	DISPENSER	CASE
63-532/S	---	616314018145	02616314018145
63-532/M	---	616314018152	02616314018152
63-532/L	---	616314018169	02616314018169
63-532/XL	---	616314018176	02616314018176
63-532/XXL	---	616314122606	02616314122604



DIMENSIONS (in/cm)

	S	M	L	XL	XXL
A	9.4 / 24.0	9.4 / 24.0	9.4 / 24.0	9.4 / 24.0	9.4 / 24.0
B	3.3 / 8.4	3.7 / 9.4	4.1 / 10.5	4.4 / 11.3	4.7 / 12.0

Palm Thickness: 0.09mm (± 0.02mm)

Finger Tip Thickness: 0.11mm (± 0.02mm)

