



SPECIFICATION SHEET

63-732

AMBI-DEX® INDUSTRIAL GRADE DISPOSABLE NITRILE GLOVES, POWDERED

- Nitrile gloves, powdered, industrial grade, 4 mil., textured
- Economical puncture resistance with great comfort, dexterity and tactile sensitivity
- Contains NO natural rubber latex proteins
- Ambidextrous for quick and easy donning
- Textured grip provides a good grip in wet and dry environments
- Nitrile is inherently anti-static and will eliminate damaging static discharge in many applications.

APPLICATIONS

- A very versatile glove for use in a broad range of applications for light hand protection from liquids and debris

TECHNICAL DATA

MATERIAL	Nitrile			
COLOR	■ Black			
CUFF STYLE	Rolled beaded			
AQL LEVEL	4.0			
SIZES	S - XL			
PACKAGING	100 pcs per dispenser box; 10 boxes per case			
CASE	14.1" x 10.0" x 9.9" / 36.0cm x 25.4cm 25.1cm			
CASE WEIGHT	S	M	L	XL
	15.1 lbs 6.8 kg	16.1 lbs 7.3 kg	17.2 lbs 7.8 kg	18.3 lbs 8.3 kg
COO	China			

ELONGATION INFORMATION

BEFORE AGING		AFTER ACCELERATED AGING	
Tensile Strength (minimum)	Elongation (minimum)	Tensile Strength (minimum)	Elongation (minimum)
(Mpa)	%	(Mpa)	%
14	500	14	400

BARCODES

ITEM	BAG	DISPENSER	CASE
■ 63-732/S	---	616314064999	02616314064997
■ 63-732/M	---	616314065002	02616314065000
■ 63-732/L	---	616314065019	02616314065017
■ 63-732/XL	---	616314065026	02616314065024



DIMENSIONS (in/cm)

	S	M	L	XL
A	9.6 / 24.5	9.6 / 24.5	9.6 / 24.5	9.6 / 24.5
B	3.3 / 8.3	3.7 / 9.5	4.1 / 10.6	4.4 / 11.2
Palm Thickness: 0.12 mm				
Cuff Thickness: 0.09mm				
Finger Tip Thickness: 0.13mm				

